



PUPM

隔壁ユニオン

Bulkhead union

黄銅製

Brass



部品番号 PART NO.	適用チューブ 外径 TUBE O.D. TO BE USED (mm)	S 六角 対辺 HEX (mm)	L ₁ (mm)	K 最大パネル厚 MAX. PANEL THICKNESS (mm)	M×P (mm)	IN (mm)	重量 WEIGHT (g)	最小内径 ORIFICE (mm)	有効断面積 EFFECTIVE SECTIONAL AREA (mm ²)	
									ナイロンチューブ NYLON TUBE	ウレタンチューブ POLYURETHANE TUBE
PUPM- 4-BSM	4	14	30	11	12×1	13	24	3	3.3	3.3
PUPM- 6-BSM	6	17	31	12	14×1	14	26	4	8.8	8.8
PUPM- 8-BSM	8	19	33	14	16×1	15	33	6	27.6	20.8
PUPM-10-BSM	10	24	42	18	20×1	19	40	8	42.9	33.9
PUPM-12-BSM	12	27	46	20	24×1	21	68	10	59.9	50.9


PNFM

隔壁メスユニオン

Bulkhead female union

黄銅製

Brass



部品番号 PART NO.	適用チューブ 外径 TUBE O.D. TO BE USED (mm)	T (Rc・M)	六角 対辺 HEX (mm)		L ₁ (mm)	L ₂ (mm)	K 最大パネル厚 MAX. PANEL THICKNESS (mm)	M×P (mm)	IN (mm)	重量 WEIGHT (g)	最小内径 ORIFICE (mm)	有効断面積 EFFECTIVE SECTIONAL AREA (mm ²)	
			S ₁	S ₂								ナイロンチューブ NYLON TUBE	ウレタンチューブ POLYURETHANE TUBE
PNFM- 4-M5-BSM	4	M5	14	14	21	5	8	12×1	13	23	3	3.1	3.1
PNFM- 4-PT1/8-BSM	4	1/8	14	14	22	7	8	12×1	13	24	3	3.3	3.3
PNFM- 6-M5-BSM	6	M5	17	17	24	4	10	14×1	14	28	4	4.2	4.2
PNFM- 6-PT1/8-BSM	6	1/8	17	17	25	6	10	14×1	14	26	3	8.8	8.8
PNFM- 6-PT1/4-BSM	6	1/4	19	17	31	12	10	14×1	14	22	6	8.8	8.8
PNFM- 8-PT1/4-BSM	8	1/4	19	19	28	7	12	16×1	15	20	6	28.2	19.6
PNFM- 8-PT3/8-BSM	8	3/8	22	19	33	12	12	16×1	15	48	6	28.2	19.6
PNFM-10-PT1/4-BSM	10	1/4	24	24	36	14	12	20×1	19	88	8	42.9	35.5
PNFM-10-PT3/8-BSM	10	3/8	24	24	36	15	12	20×1	19	75	8	42.9	35.5
PNFM-12-PT1/4-BSM	12	1/4	27	27	38	15	13	24×1	21	118	10	59.9	50.2
PNFM-12-PT3/8-BSM	12	3/8	27	27	38	15	13	24×1	21	107	10	59.9	50.2
PNFM-12-PT1/2-BSM	12	1/2	27	27	41	18	13	24×1	21	109	10	59.9	50.2