

























IMG	CODE	MATERIAL	DIMENSIONS	FLUX DENSITY	ATTRACTIVE FORCE
	ND0931	Neodymium	Φ1mmX0.5mm	140.7mT	0.021kgf
	ND0109	Neodymium	Φ1mmX1mm	178mT	0.034kgf
	ND0942	Neodymium	Φ1mmX2mm	193mT	0.04kgf
	ND0953	Neodymium	Φ1mmX3mm	196.3mT	0.041kgf
	ND0964	Neodymium	Φ1mmX4mm	197.4mT	0.042kgf
	ND0971	Neodymium	Φ1mmX5mm	198mT	0.042kgf
	ND0847	Neodymium	Φ1mmX10mm	198.7mT	0.043kgf
	ND0107	Neodymium	Φ1mmX20mm	198.9mT	0.043kgf
	ND1097	Neodymium	Φ1.2mmX5mm	273mT	0.095kgf
	ND0972	Neodymium	Φ1.5mmX0.8mm	201.8mT	0.051kgf
	ND0610	Neodymium	Φ1.5mmX1mm	221.3mT	0.062kgf
	ND0105	Neodymium	Φ1.5mmX1.5mm	247.4mT	0.077kgf
	ND0071	Neodymium	Φ1.5mmX2mm	259mT	0.085kgf
	ND0887	Neodymium	Φ1.5mmX2.5mm	265mT	0.089kgf
	ND0072	Neodymium	Φ1.5mmX3mm	268.4mT	0.091kgf
	ND0888	Neodymium	Φ1.5mmX3.5mm	270.5mT	0.092kgf
	ND0611	Neodymium	Φ1.5mmX4mm	271.9mT	0.093kgf
	ND0889	Neodymium	Φ1.5mmX4.5mm	272.9mT	0.094kgf
	ND0612	Neodymium	Φ1.5mmX5mm	273.6mT	0.094kgf
	ND0973	Neodymium	Φ1.5mmX6mm	274.5mT	0.095kgf
	ND0073	Neodymium	Φ1.5mmX8mm	275.4mT	0.096kgf
	ND0974	Neodymium	Φ1.5mmX10mm	275.9mT	0.096kgf
	ND0364	Neodymium	Φ1.5mmX20mm	276.4mT	0.096kgf
	ND0306	Neodymium	Φ2mmX0.5mm	158.2mT	0.05kgf