


## M1金具

材質：SS400 相当品, SUS304

呼び径	ねじ (R)	A (mm)	B (mm)		C (mm)	E (mm)	φD <sub>1</sub> (mm)	φD <sub>2</sub> (mm)	φD <sub>3</sub> (mm)	L (mm)		HEX (mm)
			SS	SUS						SS	SUS	
25	R1	22	12	12	58	13.0	21	25.0	27.0	92	92	35
32	R1 <sup>1</sup> / <sub>4</sub>	25	15	12	65	14.5	27	32.0	34.0	105	102	46
38	R1 <sup>1</sup> / <sub>2</sub>	26	15	14	76	14.0	31	38.0	40.3	117	116	50
50	R2	30	16	15	79	14.5	44	49.5	52.0	125	124	63
65	R2 <sup>1</sup> / <sub>2</sub>	33	18	16	99	15.0	56	62.5	65.0	150	140	80
75	R3	38	18	16	114	17.0	69	74.5	77.5	170	160	90
※100	R4	45	22	—	153	21.5	88	97.0	102.0	220	—	120

※印は SUS 製がありません




## F5金具

材質：SS400 相当品, SUS304

呼び径	ねじ (G)	A (mm)		B (mm)	C (mm)	φD <sub>1</sub> (mm)	φD <sub>2</sub> (mm)	φD <sub>3</sub> (mm)	L (mm)		HEX (mm)	山数
		SS	SUS						SS	SUS		
25	G1	75	75	28	13.0	21.0	25.0	27.0	86	86	38	3
32	G1 <sup>1</sup> / <sub>4</sub>	85	85	31	14.5	28.0	32.0	34.0	96	96	50	3
38	G1 <sup>1</sup> / <sub>2</sub>	96	96	31	14.0	33.0	38.0	40.3	107	107	60	4
50	G2	99	99	33	14.5	44.5	49.5	52.0	112	112	70	4
65	G2 <sup>1</sup> / <sub>2</sub>	125	108	40	15.0	56.0	62.5	65.0	139	131	90	5
75	G3	141	124	42	17.0	69.0	74.5	77.5	156	148	100	5
※100	G4	188	—	55	21.5	90.0	97.0	102.0	208	—	130	5

※印は SUS 製がありません




## M2金具 (パッキンシートタイプ)

材質：SS400 相当品

呼び径	ねじ (G)	L (mm)	A (mm)	B (mm)	φD <sub>3</sub> (mm)	HEX (mm)
12	G <sup>1</sup> / <sub>2</sub>	74	18	44	14	22
19	G <sup>3</sup> / <sub>4</sub>	85	20	53	20.5	27
25	G1	92	22	58	27	35
32	G <sup>1</sup> / <sub>4</sub>	105	25	65	34	46
38	G <sup>1</sup> / <sub>2</sub>	118	26	76	40.5	50
50	G2	125	30	79	52	63

パッキンシートは別途ご用意ください。



## F1金具 (パッキンシートタイプ)

材質：SS400 相当品

呼び径	ねじ (G)	A (mm)	B (mm)	φD <sub>1</sub> (mm)	φD <sub>2</sub> (mm)	φD <sub>3</sub> (mm)	L (mm)	HEX (mm)
25	G1	28	13.0	21.0	25.0	27.0	86	38
32	G1 <sup>1</sup> / <sub>4</sub>	31	14.5	28.0	32.0	34.0	96	50
38	G1 <sup>1</sup> / <sub>2</sub>	31	14.0	33.0	38.0	40.3	107	60
50	G2	33	14.5	44.5	49.5	52.0	112	70
65	G2 <sup>1</sup> / <sub>2</sub>	40	15.0	56.0	62.5	65.0	139	90
75	G3	42	17.0	69.0	74.5	77.5	156	100
100	G4	55	21.5	90.0	97.0	102.0	208	130

パッキンシートは別途ご用意ください。

