

加工用途	形状	呼び記号	在庫								シート サイズ	寸法 (mm)							
			コーティング		サーメット		超硬		CBN			CW		RER/L	CDX	*2			
			VP10RT	VP20RT	MY5015	NX2525	RT9010	RT9020	BC8110	MB8025		刃幅	公差			L	LE		
突切り加工用	<p>本図は右勝手(R)を示す。</p>	GY2M0200D020R05-GM	●	●							D	2.00	±0.03	0.2	19.5	20.80	—		
		GY2M0200D020L05-GM	●	●								D	2.00	±0.03	0.2	19.5	20.80	—	
		GY2M0250E020R05-GM	●	●								E	2.50	±0.03	0.2	19.5	20.825	—	
		GY2M0250E020L05-GM	●	●								E	2.50	±0.03	0.2	19.5	20.825	—	
		GY2M0300F030R05-GM	●	●								F	3.00	±0.03	0.3	19.5	20.85	—	
		GY2M0300F030L05-GM	●	●								F	3.00	±0.03	0.3	19.5	20.85	—	
		GY2M0400G030R05-GM	●	●								G	4.00	±0.04	0.3	24.5	25.85	—	
		GY2M0400G030L05-GM	●	●								G	4.00	±0.04	0.3	24.5	25.85	—	
		GY2M0500H040R05-GM	●	●								H	5.00	±0.04	0.4	24.5	25.95	—	
		GY2M0500H040L05-GM	●	●								H	5.00	±0.04	0.4	24.5	25.95	—	
溝入れ加工用		GY1G0200D020N-GFGS								●	●	D	2.00	±0.03	0.2	—	20.70	2.7	
		GY1G0239E020N-GFGS									●	●	E	2.39	±0.03	0.2	—	20.70	2.7
		GY1G0250E020N-GFGS									●	●	E	2.50	±0.03	0.2	—	20.70	2.7
		GY1G0300F020N-GFGS									●	●	F	3.00	±0.03	0.2	—	20.70	2.7
		GY1G0318F020N-GFGS									●	●	F	3.18	±0.03	0.2	—	20.70	2.7
		GY1G0400G020N-GFGS									●	●	G	4.00	±0.03	0.2	—	25.65	2.7
		GY1G0475H020N-GFGS									●	●	H	4.75	±0.03	0.2	—	25.65	2.7
		GY1G0500H020N-GFGS									●	●	H	5.00	±0.03	0.2	—	25.65	2.7
		GY1G0600J020N-GFGS									●	●	J	6.00	±0.03	0.2	—	25.65	2.7
		多機能加工用		GY2G0200D020N-MF	●	●	●	●						D	2.00	±0.02	0.2	19.5	21.05
*1GY2G0224D015N-MF	●			●	●	●							D	2.24	±0.02	0.15	19.8	21.05	—
GY2G0239E020N-MF	●			●	●	●							E	2.39	±0.02	0.2	19.2	21.05	—
GY2G0250E020N-MF	●			●	●	●							E	2.50	±0.02	0.2	19.4	21.05	—
*1GY2G0274E020N-MF	●			●	●	●							E	2.74	±0.02	0.2	19.7	21.05	—
GY2G0300F020N-MF	●			●	●	●							F	3.00	±0.02	0.2	19.5	21.05	—
GY2G0300F040N-MF	●			●	●	●							F	3.00	±0.02	0.4	19.3	21.05	—
GY2G0318F020N-MF	●			●	●	●							F	3.18	±0.02	0.2	19.5	21.05	—
GY2G0318F040N-MF	●			●	●	●							F	3.18	±0.02	0.4	19.3	21.05	—
*1GY2G0324F020N-MF	●			●	●	●							F	3.24	±0.02	0.2	19.5	21.05	—
GY2G0400G020N-MF	●			●	●	●							G	4.00	±0.02	0.2	24.9	25.95	—
GY2G0400G040N-MF	●			●	●	●							G	4.00	±0.02	0.4	24.7	25.95	—
GY2G0400G080N-MF	●			●	●	●							G	4.00	±0.02	0.8	24.3	25.95	—
*1GY2G0424G020N-MF	●			●	●	●							G	4.24	±0.02	0.2	24.9	25.95	—
GY2G0475H020N-MF	●			●	●	●							H	4.75	±0.02	0.2	24.4	25.95	—
GY2G0475H040N-MF	●			●	●	●							H	4.75	±0.02	0.4	24.2	25.95	—
GY2G0475H080N-MF	●			●	●	●							H	4.75	±0.02	0.8	23.8	25.95	—
GY2G0500H020N-MF	●			●	●	●							H	5.00	±0.02	0.2	24.4	25.95	—
GY2G0500H040N-MF	●			●	●	●							H	5.00	±0.02	0.4	24.2	25.95	—
GY2G0500H080N-MF	●			●	●	●							H	5.00	±0.02	0.8	23.8	25.95	—
*1GY2G0524H020N-MF	●			●	●	●							H	5.24	±0.02	0.2	24.4	25.95	—
GY2G0600J020N-MF	●			●	●	●							J	6.00	±0.02	0.2	24.4	25.95	—
GY2G0600J040N-MF	●			●	●	●							J	6.00	±0.02	0.4	24.2	25.95	—
GY2G0600J080N-MF	●			●	●	●							J	6.00	±0.02	0.8	23.8	25.95	—
*1GY2G0631J020N-MF	●			●	●	●							J	6.31	±0.02	0.2	24.4	25.95	—
GY2G0635J020N-MF	●			●	●	●							J	6.35	±0.02	0.2	24.4	25.95	—
GY2G0635J040N-MF	●	●	●	●							J	6.35	±0.02	0.4	24.2	25.95	—		
GY2G0635J080N-MF	●	●	●	●							J	6.35	±0.02	0.8	23.8	25.95	—		

*1 サークリップ対応刃幅

F

溝入れ・突切り加工