

















### 100型切断火口 中圧式

火口名	番丁	Stock.No.	火口形状	使用ガス	用途と特性
102	00~8	DB11101B~L		アセチレン	S
102-D5		DB11103B~L			D
102-D7		DB11104B~L			D

103	00~8	DB11701B~L		エチレン	S
103-D5		DB11702B~L			D
103-D7		DB11703B~L			D

105A	00~8	DB11901B~L		水素	S
105A-5		DB11902B~L			D
105A-7	00~5	DB11903B~H			D
105A-0		DB11904B~H			S
105A-05		DB11905B~H			D
105A-07		DB11407B~H			D

106	00~8	DB11401B~L		LPG	S
106-D5		DB11402B~L			D
106-D7		DB11403B~L			D
106-0		DB11404B~L			S
106-05		DB11405B~L			D
106-07		DB11406B~L			D
106-M		DB11407B~L			S
106-M5		DB11408B~L			D
106-M7		DB11409B~L			D
106-S		DB11519B~L			S