



ステッキツイン

CB

(内径加工用)



規格は右勝手(R)のみです。

呼 び 記 号	在庫				ブレーカ	DMIN *1		寸法(mm)								
	コーティング			超硬				RE	DCON MS	LF	L20	LDRED	WF	WF2	H	Z
	NEW	NEW				l/d≤3	l/d>3									
	MS7025	MS9025	VP15TF	TF15												
CB02RS			●	●	なし	2.2	3.6	0.05	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
CB02RS-B	●	●	●	●	付き	2.2	4.6	0.05	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
CB02RS-01			●	●	なし	2.2	3.6	0.1	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
CB02RS-01B	●	●	●	●	付き	2.2	4.6	0.1	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
NEW CB02RS-015B	●	●			付き	2.2	4.6	0.15	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
CB02RS-02			●	●	なし	2.2	3.6	0.2	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
CB02RS-02B	●	●	●	●	付き	2.2	4.6	0.2	2.0	50	5.0	6.0	1.0	0.25	1.8	1.4
NEW CB025RS-B	●	●			付き	2.7	4.7	0.05	2.5	50	6.25	7.5	1.25	0.30	2.25	1.8
NEW CB025RS-01B	●	●			付き	2.7	4.7	0.1	2.5	50	6.25	7.5	1.25	0.30	2.25	1.8
NEW CB025RS-015B	●	●			付き	2.7	4.7	0.15	2.5	50	6.25	7.5	1.25	0.30	2.25	1.8
NEW CB025RS-02B	●	●			付き	2.7	4.7	0.2	2.5	50	6.25	7.5	1.25	0.30	2.25	1.8
CB03RS			●	●	なし	3.2	4.2	0.05	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
CB03RS-B	●	●	●	●	付き	3.2	4.8	0.05	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
CB03RS-01			●	●	なし	3.2	4.2	0.1	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
CB03RS-01B	●	●	●	●	付き	3.2	4.8	0.1	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
NEW CB03RS-015B	●	●			付き	3.2	4.8	0.15	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
CB03RS-02			●	●	なし	3.2	4.2	0.2	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
CB03RS-02B	●	●	●	●	付き	3.2	4.8	0.2	3.0	50	7.5	9.0	1.5	0.35	2.7	2.3
NEW CB035RS-B	●	●			付き	3.7	5.2	0.05	3.5	60	8.75	10.5	1.75	0.40	3.15	2.6
NEW CB035RS-01B	●	●			付き	3.7	5.2	0.1	3.5	60	8.75	10.5	1.75	0.40	3.15	2.6
NEW CB035RS-015B	●	●			付き	3.7	5.2	0.15	3.5	60	8.75	10.5	1.75	0.40	3.15	2.6
NEW CB035RS-02B	●	●			付き	3.7	5.2	0.2	3.5	60	8.75	10.5	1.75	0.40	3.15	2.6
CB04RS			●	●	なし	4.2	5.1	0.05	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
CB04RS-B	●	●	●	●	付き	4.2	5.5	0.05	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
CB04RS-01			●	●	なし	4.2	5.1	0.1	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
CB04RS-01B	●	●	●	●	付き	4.2	5.5	0.1	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
NEW CB04RS-015B	●	●			付き	4.2	5.5	0.15	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
CB04RS-02			●	●	なし	4.2	5.1	0.2	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
CB04RS-02B	●	●	●	●	付き	4.2	5.5	0.2	4.0	60	10.0	12.0	2.0	0.45	3.6	3.1
NEW CB045RS-B	●	●			付き	4.7	6.0	0.05	4.5	70	11.25	13.5	2.25	0.50	4.05	3.4
NEW CB045RS-01B	●	●			付き	4.7	6.0	0.1	4.5	70	11.25	13.5	2.25	0.50	4.05	3.4
NEW CB045RS-015B	●	●			付き	4.7	6.0	0.15	4.5	70	11.25	13.5	2.25	0.50	4.05	3.4
NEW CB045RS-02B	●	●			付き	4.7	6.0	0.2	4.5	70	11.25	13.5	2.25	0.50	4.05	3.4
CB05RS			●	●	なし	5.2	6.0	0.05	5	70	12.5	15.0	2.5	0.55	4.5	3.9
CB05RS-B	●	●	●	●	付き	5.2	6.4	0.05	5	70	12.5	15.0	2.5	0.55	4.5	3.9
NEW CB05RS-015B	●	●			付き	5.2	6.4	0.15	5	70	12.5	15.0	2.5	0.55	4.5	3.9
CB05RS-02			●	●	なし	5.2	6.0	0.2	5	70	12.5	15.0	2.5	0.55	4.5	3.9
CB05RS-02B	●	●	●	●	付き	5.2	6.4	0.2	5	70	12.5	15.0	2.5	0.55	4.5	3.9
CB06RS			●	●	なし	6.2	7.2	0.05	6	75	12.5	18.0	3.0	0.65	5.4	4.7
CB06RS-B	●	●	●	●	付き	6.2	7.3	0.05	6	75	12.5	18.0	3.0	0.65	5.4	4.7
CB06RS-02			●	●	なし	6.2	7.2	0.2	6	75	12.5	18.0	3.0	0.65	5.4	4.7
CB06RS-02B	●	●	●	●	付き	6.2	7.8	0.2	6	75	12.5	18.0	3.0	0.65	5.4	4.7

*1 DMIN：最小加工径

*2 ブレーカ付きは、ブレーカ前寸法を示します。

● = NEW

●：標準在庫品

(ステッキツインは、1ケース 1 個入りです)