



IMX-C3A

アルミニウム合金加工用3枚刃ラジアスヘッド



炭素鋼・合金鋼・鋳鉄 ($<30\text{HRC}$)	工具鋼・プリハードン鋼・高硬度鋼 ($\leq 45\text{HRC}$)	高硬度鋼 ($\leq 55\text{HRC}$)	高硬度鋼 ($> 55\text{HRC}$)	オーステナイト系 ステンレス鋼	チタン合金 耐熱合金	銅合金	アルミニウム合金
							◎



RE ≤ 5				
± 0.020				



DC ≤ 12	DC > 12			
0 - 0.020	0 - 0.030			

●アルミニウム合金加工用にすくい角を大きくした刃形の採用とすくい面の鏡面処理により高能率加工を実現します。

(mm)

呼び記号	DC	RE	APMX	LH	DCON	刃数	材種	図
							ET2020	
IMX10C3A100R10008	10	1	8	16	9.7	3	●	1
IMX10C3A100R25008	10	2.5	8	16	9.7	3	●	1
IMX10C3A120R10010	12	1	10.1	19	9.7	3	●	2
IMX12C3A120R10009	12	1	9.6	19	11.7	3	●	1
IMX12C3A120R32009	12	3.2	9.6	19	11.7	3	●	1
IMX12C3A140R10011	14	1	11.7	22.5	11.7	3	●	2
IMX16C3A160R10012	16	1	12.8	24	15.5	3	●	1
IMX16C3A160R32012	16	3.2	12.8	24	15.5	3	●	1
IMX16C3A180R32014	18	3.2	14.9	27	15.5	3	●	2
IMX20C3A200R10016	20	1	16	30	19.5	3	●	1
IMX20C3A200R32016	20	3.2	16	30	19.5	3	●	1
IMX20C3A220R32018	22	3.2	18.6	33	19.5	3	●	2
IMX25C3A250R10020	25	1	20	37.5	24.5	3	●	1
IMX25C3A250R32020	25	3.2	20	37.5	24.5	3	●	1
IMX25C3A250R50020	25	5	20	37.5	24.5	3	●	1
IMX25C3A280R32023	28	3.2	23.4	41.5	24.5	3	●	2

注1) ヘッドとホルダは締結サイズが同じものをご使用ください。(4ページ 参照)