


COMBINATION WRENCH

No.	S*	D <sub>1</sub>	D <sub>2</sub>	T <sub>1</sub>	T <sub>2</sub>	L	▼g	📦	小売参考価格
MS2-032	3.2	8	7.5	3	3	75	6	5	¥ 890
MS2-04	4	9	8.3	3	4	80	8	5	¥ 890
MS2-045	4.5	10	8.8	3	4	85	10	5	¥ 890
MS2-05	5	11	9.3	3	4.5	90	11	5	¥ 890
MS2-055	5.5	12.4	9.9	3	4.5	96	13	5	¥ 890
MS2-06	6	13.2	10.4	3	4.5	96	14	5	¥ 890
MS2-07	7	15.4	11.9	3.5	5	111	20	5	¥ 890
MS2-08	8	17.3	12.9	4	5.5	126	28	5	¥ 910
MS2-09	9	19.5	14.4	4.5	6	136	36	5	¥ 930
MS2-10	10	21.5	16.1	4.5	6.5	151	42	5	¥ 1,050
MS2-11	11	23.5	17.1	5	7	161	55	5	¥ 1,220
MS2-12	12	25.5	18.1	5.5	7.5	170	65	5	¥ 1,220
MS2-13	13	27.5	19.1	6	8.5	188	85	5	¥ 1,480
MS2-14	14	29.5	20.6	6	9.5	190	98	5	¥ 1,480
MS2-15	15	31.4	22.6	7	10	200	119	5	¥ 1,530
MS2-16	16	33.4	23.6	7	10.5	215	134	5	¥ 1,530
MS2-17	17	36	25.1	7	10.5	225	153	5	¥ 1,600
MS2-18	18	38	26.6	8	11.5	241	184	5	¥ 1,790
MS2-19	19	40	27.6	7.5	12	256	205	5	¥ 1,840
MS2-20	20	42	29.6	8	12	271	234	5	¥ 2,060
MS2-21	21	44	30.6	8	13	289	267	5	¥ 2,070
MS2-22	22	46	32.1	8.5	13.5	304	305	5	¥ 2,490
MS2-23	23	48	33.6	8.5	14.5	311	331	5	¥ 2,620
MS2-24	24	50	35.1	9	15	337	380	5	¥ 3,000
MS2-25	25	52	36.1	9	15.5	351	423	5	¥ 3,340
MS2-26	26	54	37.6	9	16	371	466	5	¥ 3,700
MS2-27	27	55.7	39.1	9	16.5	381	502	5	¥ 3,830
MS2-28	28	57.7	40.6	9.5	17	401	561	5	¥ 5,020
MS2-29	29	60	43.6	10	18	421	650	1	¥ 5,140
MS2-30	30	61.7	43.6	10	18	446	687	1	¥ 5,950
MS2-31	31	63.7	45.6	10.5	18	462	790	1	¥ 6,560
MS2-32	32	65.7	46.6	10.5	18	471	836	1	¥ 6,880
MS2-33	33	67.7	47.6	11	20	477	904	1	¥ 7,550
MS2-34	34	69.7	52.1	11	21	480	1,030	1	¥ 8,200
MS2-35	35	72	52.1	12	21	481	1,070	1	¥ 8,880
MS2-36	36	74	52.1	12	21	501	1,155	1	¥ 11,400
MS2-38	38	78	54.6	13.5	22	521	1,382	1	¥ 12,400
MS2-41	41	84	59.1	14	24.5	542	1,680	1	¥ 12,800
MS2-46	46	94	66.1	14	26	562	2,142	1	¥ 15,800

※めがね側の5mm以下は六角口径です。

コンビネーションレンチ




COMBINATION WRENCH

No.	S(in)*	D <sub>1</sub>	D <sub>2</sub>	T <sub>1</sub>	T <sub>2</sub>	L	▼g	📦	小売参考価格
MS2-1/8	1/8	8	7.3	3	3	75	6	5	¥ 1,370
MS2-5/32	5/32	9	8.3	3	4	80	8	5	¥ 1,370
MS2-3/16	3/16	10	8.8	3	4	85	10	5	¥ 1,370
MS2-13/64	13/64	11	9.3	3	4.5	90	11	5	¥ 1,370
MS2-7/32	7/32	12.4	9.9	3	4.5	95.9	13	5	¥ 1,370
MS2-15/64	15/64	13.2	10.4	3	4.5	95.8	14	5	¥ 1,370
MS2-1/4	1/4	13.2	10.4	3	4.5	95.8	14	5	¥ 1,370
MS2-9/32	9/32	15.4	11.9	3.5	5	111	20	5	¥ 1,440
MS2-5/16	5/16	17.3	12.9	4	5.5	126.2	28	5	¥ 1,450
MS2-11/32	11/32	19.5	14.4	4.5	6	136.1	36	5	¥ 1,470
MS2-3/8	3/8	21.5	16.1	4.5	6.5	150.4	42	5	¥ 1,470
MS2-7/16	7/16	23.5	17.1	5	7	161	55	5	¥ 1,640
MS2-1/2	1/2	27.5	19.1	6	8.5	187.4	85	5	¥ 1,950
MS2-9/16	9/16	29.5	20.6	6	9.5	190.2	98	5	¥ 1,990
MS2-19/32	19/32	31.4	22.6	7	10	200.3	119	5	¥ 2,080
MS2-5/8	5/8	33.4	23.6	7	10.5	215.3	134	5	¥ 2,130
MS2-11/16	11/16	36	25.1	7	10.5	225.2	153	5	¥ 2,180
MS2-3/4	3/4	40	27.6	7.5	12	255.3	205	5	¥ 2,510
MS2-25/32	25/32	42	29.6	8	12	270.4	234	5	¥ 2,730
MS2-13/16	13/16	44	30.6	8	13	288.4	267	5	¥ 2,840
MS2-7/8	7/8	46	32.1	8.5	13.5	303.5	305	5	¥ 3,400
MS2-15/16	15/16	50	35.1	9	15	336.5	380	5	¥ 4,260
MS2-1	1	52	36.1	9	15.5	350.5	423	5	¥ 4,660
MS2-1-1/16	1-1/16	55.7	39.1	9	16.5	380.7	502	5	¥ 5,490
MS2-1-1/8	1-1/8	60	43.6	10	18	420.5	650	5	¥ 7,190
MS2-1-3/16	1-3/16	61.7	43.6	10	18	445.8	687	5	¥ 8,320
MS2-1-1/4	1-1/4	65.7	46.6	10.5	18	470.7	836	5	¥ 9,640
MS2-1-5/16	1-5/16	67.7	47.6	11	20	476.6	904	5	¥ 10,600
MS2-1-3/8	1-3/8	72	52.1	12	21	480.7	1,070	1	¥ 12,500
MS2-1-7/16	1-7/16	74	52.1	12	21	500.9	1,155	1	¥ 15,900
MS2-1-1/2	1-1/2	78	54.6	13.5	22	520.9	1,382	1	¥ 17,400

※めがね側の13/64in以下は六角口径です。

コンビネーションレンチ



品名の下に製品の機能を表す機能マークを入れています。マークの意味は P.4~5をご参照ください。

✖ めがね側の製品は手動用です。インパクトレンチ等の動力工具では使用しないでください。

🔥 このマークのついている製品は在庫を確認の上ご注文ください。

(マークの例: 36, 39, POWERFIT, 36, 39, リバート, 六角, プラス)

表示価格は「小売参考価格」であり消費税は含まれておりません。