


# 7°ポジティブインサート(穴つき) E級、G級精度



仕上げ切削 F	仕上げ切削 F	仕上げ切削 F
R/L-F	FS-P	R/L-SRF
軽切削 L		
LS-P		

(mm)

呼び記号	切削領域	MS6015	MS7025	MS9025	IC	S	RE*	D1
TCGT060101MR-F	F	●			3.97	1.59	0.1	2.3
TCGT060101ML-F	F	●			3.97	1.59	0.1	2.3
TCGT060102MR-F	F	●			3.97	1.59	0.2	2.3
TCGT060102ML-F	F	●			3.97	1.59	0.2	2.3
TCGT060104MR-F	F	●			3.97	1.59	0.4	2.3
TCGT060104ML-F	F	●			3.97	1.59	0.4	2.3
VCGT110301M-FS-P	F		●	●	6.35	3.18	0.1	2.8
VCGT110302M-FS-P	F		●	●	6.35	3.18	0.2	2.8
VCGT110304M-FS-P	F			●	6.35	3.18	0.4	2.8
VCET080202MR-SRF	F			●	4.76	2.38	0.2	2.4
VCET080202ML-SRF	F			●	4.76	2.38	0.2	2.4
VCET080204MR-SRF	F			●	4.76	2.38	0.4	2.4
VCET080204ML-SRF	F			●	4.76	2.38	0.4	2.4
VCET110301MR-SRF	F			●	6.35	3.18	0.1	2.8
VCET110301ML-SRF	F			●	6.35	3.18	0.1	2.8
VCET110302MR-SRF	F			●	6.35	3.18	0.2	2.8
VCET110302ML-SRF	F			●	6.35	3.18	0.2	2.8
VCET110304MR-SRF	F			●	6.35	3.18	0.4	2.8
VCET110304ML-SRF	F			●	6.35	3.18	0.4	2.8
VCGT110301M-LS-P	L		●	●	6.35	3.18	0.1	2.8
VCGT110302M-LS-P	L		●	●	6.35	3.18	0.2	2.8
VCGT110304M-LS-P	L		●	●	6.35	3.18	0.4	2.8
VCGT130301M-LS-P	L			●	7.94	3.18	0.1	3.4
VCGT130302M-LS-P	L			●	7.94	3.18	0.2	3.4
VCGT130304M-LS-P	L			●	7.94	3.18	0.4	3.4

\* RE値は最大値を示します。

● = NEW