

標準在庫型番 (ポジ)

形状	型番	寸法(mm)					PR115S	PR120S	PR153S
		内接円直径	厚み	穴径	コーナR (RE)	逃げ角			
 仕上げ・シャープエッジ・鏡面仕様	CCGT 0602005MFP-SKS				<0.05		●	●	●
	060201MFP-SKS	6.35	2.38	3	<0.1	7°	●	●	●
	060202MFP-SKS				<0.2		●	●	●
	CCGT 09T3005MFP-SKS				<0.05		●	●	●
	09T301MFP-SKS	9.525	3.97	4.7	<0.1	7°	●	●	●
	09T302MFP-SKS				<0.2		●	●	●
	09T304MFP-SKS				<0.4		●	●	●
	CCGT 060201MFP-SK	6.35	2.38	3	<0.1	7°	●	●	●
	060202MFP-SK				<0.2		●	●	●
 仕上げ・シャープエッジ・鏡面仕様	060204MFP-SK				<0.4		●	●	●
	CCGT 09T301MFP-SK				<0.1		●	●	●
	09T302MFP-SK	9.525	3.97	4.7	<0.2	7°	●	●	●
	09T304MFP-SK				<0.4		●	●	●
	CCGT 060201MFP-GQ	6.35	2.38	3	<0.1	7°	●	●	●
	060202MFP-GQ				<0.2		●	●	●
	060204MFP-GQ				<0.4		●	●	●
	CCGT 09T301MFP-GQ				<0.1		●	●	●
	09T302MFP-GQ	9.525	3.97	4.7	<0.2	7°	●	●	●
 仕上げ～中・シャープエッジ・鏡面仕様	09T304MFP-GQ				<0.4		●	●	●
	CCMT 09T304MQ	9.525	3.97	4.7	0.4	7°	●	●	●
	09T308MQ				0.8		●	●	●
	DCGT 0702005MFP-SKS	6.35	2.38	3	<0.05	7°	●	●	●
	070201MFP-SKS				<0.1		●	●	●
	070202MFP-SKS				<0.2		●	●	●
	DCGT 11T3005MFP-SKS	9.525	3.97	4.7	<0.05	7°	●	●	●
	11T301MFP-SKS				<0.1		●	●	●
	11T302MFP-SKS				<0.2		●	●	●
 仕上げ・シャープエッジ・鏡面仕様	11T304MFP-SKS				<0.4		●	●	●

形状	型番	寸法(mm)					PR115S	PR120S	PR153S
		内接円直径	厚み	穴径	コーナR (RE)	逃げ角			
 仕上げ・シャープエッジ・鏡面仕様	DCGT 070201MFP-SK	6.35	2.38	3	<0.1	7°	●	●	●
	070202MFP-SK				<0.2		●	●	●
	070204MFP-SK				<0.4		●	●	●
	DCGT 11T301MFP-SK	9.525	3.97	4.7	<0.1	7°	●	●	●
	11T302MFP-SK				<0.2		●	●	●
	11T304MFP-SK				<0.4		●	●	●
	DCGT 070201MFP-GQ	6.35	2.38	3	<0.1	7°	●	●	●
	070202MFP-GQ				<0.2		●	●	●
	070204MFP-GQ				<0.4		●	●	●
 仕上げ～中・シャープエッジ・鏡面仕様	DCGT 11T301MFP-GQ	9.525	3.97	4.7	<0.1	7°	●	●	●
	11T302MFP-GQ				<0.2		●	●	●
	11T304MFP-GQ				<0.4		●	●	●
	DCMT 070202MQ	6.35	2.38	3	0.2	7°	●	●	●
	070204MQ				0.4		●	●	●
	DCMT 11T304MQ	9.525	3.97	4.7	0.4	7°	●	●	●
	11T308MQ				0.8		●	●	●
	VCGT 110301MFP-SKS	6.35	3.18	2.8	<0.1	7°	●	●	●
	110302MFP-SKS				<0.2		●	●	●
 仕上げ・シャープエッジ・鏡面仕様	110304MFP-SKS				<0.4		●	●	●
	VPGT 110301MFP-SKS	6.35	3.18	3	<0.1	11°	●	●	●
	110302MFP-SKS				<0.2		●	●	●
	110304MFP-SKS				<0.4		●	●	●

●：標準在庫

コーナR (RE) 寸法が不等号 (例: <0.1, <0.2 など) で表示されていますチップは、コーナR (RE) がマイナス公差の製品を示します

