

MSMHZD

エムスターエンドミル

3枚刃エムスタースロッシングエンドミル(M)

製品情報



対象被削材






技術資料 >> 1995

ISO13399記号 >> 1966

マークの見方 >> 670

エンドミル選定目安表 >> 674



| | | | | |
|--|--------------|---------------|----------------|-------------|
| | DC ≤ 12 | DC > 12 | | |
| | 0 -0.020 | 0 -0.030 | | |
| | 4 ≤ DCON ≤ 6 | 8 ≤ DCON ≤ 10 | 12 ≤ DCON ≤ 16 | DCON = 20 |
| | 0 -0.008 | 0 -0.009 | 0 -0.011 | 0 -0.013 |

●標準在庫 単位:mm

| 呼び記号 | DC | APMX | LF | DCON | 刃数 | 在庫 | 図番 |
|-------------|-----|------|-----|------|----|----|----|
| MSMHZDD0100 | 1 | 2 | 45 | 4 | 3 | ● | 1 |
| MSMHZDD0150 | 1.5 | 3 | 45 | 4 | 3 | ● | 1 |
| MSMHZDD0200 | 2 | 4 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0250 | 2.5 | 5 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0300 | 3 | 6 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0350 | 3.5 | 8 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0400 | 4 | 8 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0450 | 4.5 | 10 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0500 | 5 | 10 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0550 | 5.5 | 13 | 50 | 6 | 3 | ● | 1 |
| MSMHZDD0600 | 6 | 13 | 60 | 6 | 3 | ● | 2 |
| MSMHZDD0650 | 6.5 | 16 | 60 | 8 | 3 | ● | 1 |
| MSMHZDD0700 | 7 | 16 | 60 | 8 | 3 | ● | 1 |
| MSMHZDD0750 | 7.5 | 16 | 60 | 8 | 3 | ● | 1 |
| MSMHZDD0800 | 8 | 19 | 70 | 8 | 3 | ● | 2 |
| MSMHZDD0850 | 8.5 | 19 | 70 | 10 | 3 | ● | 1 |
| MSMHZDD0900 | 9 | 19 | 70 | 10 | 3 | ● | 1 |
| MSMHZDD0950 | 9.5 | 19 | 70 | 10 | 3 | ● | 1 |
| MSMHZDD1000 | 10 | 22 | 80 | 10 | 3 | ● | 2 |
| MSMHZDD1100 | 11 | 22 | 80 | 12 | 3 | ● | 1 |
| MSMHZDD1200 | 12 | 26 | 90 | 12 | 3 | ● | 2 |
| MSMHZDD1300 | 13 | 26 | 90 | 12 | 3 | ● | 3 |
| MSMHZDD1400 | 14 | 26 | 90 | 12 | 3 | ● | 3 |
| MSMHZDD1500 | 15 | 26 | 110 | 16 | 3 | ● | 1 |
| MSMHZDD1600 | 16 | 30 | 110 | 16 | 3 | ● | 2 |
| MSMHZDD2000 | 20 | 32 | 140 | 20 | 3 | ● | 2 |

超硬
スクエア
ボール
ラジアス
テーパ
ソリッドエンドミル