


MFPN45 フェースミル



● ホルダ寸法

型番	在庫		刃数	寸法(mm)												形状	重量(kg)	シート		
	R	L		DC	DCX	DCSFMS	DCB	DCCB ₁	DCCB ₂	LF	CDBP	KDP	KWW	DCCB ₃	DCCB ₄					
インロー部 インチ仕様	コースピッチ	MFPN 45080%-5T	●	●	5	80	93	60	25.4	22	13							Fig. 1	1.1	有
		45100%-6T	●	●	6	100	113	70	31.75	48								Fig. 2	1.4	
		45125%-7T	●	●	7	125	138	87	38.1	58								Fig. 2	2.6	
		45160%-8T	●	●	8	160	173	102	50.8	72								Fig. 2	4.0	
		45200R-10T	●		10	200	213											Fig. 3	6.7	
		45250R-12T	●		12	250	263	142	47.625	110	101.6			18	26		Fig. 3	9.4		
		45315R-14T	受		14	315	328	220				80					Fig. 4	21.2		
	クロスピッチ	MFPN 45080R-6T	●		6	80	93	60	25.4	22	13							Fig. 1	1.1	無
		45100R-8T	●		8	100	113	70	31.75	48								Fig. 1	1.4	
		45125R-10T	●		10	125	138	87	38.1	58								Fig. 2	2.7	
		45160R-12T	●		12	160	173	102	50.8	72								Fig. 2	4.0	
		45200R-14T	●		14	200	213											Fig. 3	6.9	
		45250R-16T	●		16	250	263	142	47.625	110	101.6			18	26		Fig. 3	9.6		
		45315R-18T	受		18	315	328	220				80					Fig. 4	21.5		
	エキストラクロスピッチ	MFPN 45080R-8T	●		8	80	93	60	25.4	22	13							Fig. 1	1.1	無
		45100R-10T	●		10	100	113	70	31.75	48								Fig. 1	1.3	
		45125R-13T	●		13	125	138	87	38.1	58								Fig. 2	2.7	
		45160R-16T	●		16	160	173	102	50.8	72								Fig. 2	4.0	
45200R-18T		●		18	200	213											Fig. 3	6.9		
45250R-20T		●		20	250	263	142	47.625	110	101.6			18	26		Fig. 3	9.6			
ミリ仕様	コースピッチ	MFPN 45063R-4T-M	●		4	63	76	47	22	19	11	40	21	6.3	10.4			Fig. 1	0.5	有
		45080R-5T-M	●		5	80	93	60	27	22	13							Fig. 1	1.1	
		45100R-6T-M	●		6	100	113	70	32	48								Fig. 2	1.4	
		45125R-7T-M	●		7	125	138	87		58								Fig. 2	2.6	
		45160R-8T-M	●		8	160	173	102	40	68	66.7			14	20			Fig. 3	3.8	
		45200R-10T-M	●		10	200	213											Fig. 3	6.4	
		45250R-12T-M	●		12	250	263	142	60	110	101.6			18	26			Fig. 3	9.1	
		45315R-14T-M	受		14	315	328	220				80						Fig. 4	21.3	
	クロスピッチ	MFPN 45063R-5T-M	●		5	63	76	47	22	19	11	40	21	6.3	10.4			Fig. 1	0.5	無
		45080R-6T-M	●		6	80	93	60	27	22	13							Fig. 1	1.0	
		45100R-8T-M	●		8	100	113	70	32	48								Fig. 2	1.4	
		45125R-10T-M	●		10	125	138	87		58								Fig. 2	2.5	
		45160R-12T-M	●		12	160	173	102	40	68	66.7			14	20			Fig. 3	3.8	
		45200R-14T-M	●		14	200	213											Fig. 3	6.5	
		45250R-16T-M	●		16	250	263	142	60	110	101.6			18	26			Fig. 3	9.1	
		45315R-18T-M	受		18	315	328	220				80						Fig. 4	21.7	
	エキストラクロスピッチ	MFPN 45063R-6T-M	●		6	63	76	47	22	19	11	40	21	6.3	10.4			Fig. 1	0.5	無
		45080R-8T-M	●		8	80	93	60	27	22	13							Fig. 1	1.1	
45100R-10T-M		●		10	100	113	70	32	48								Fig. 2	1.3		
45125R-13T-M		●		13	125	138	87		58								Fig. 2	2.6		
45160R-16T-M		●		16	160	173	102	40	68	66.7			14	20			Fig. 3	3.9		
45200R-18T-M		●		18	200	213											Fig. 3	6.6		
45250R-20T-M		●		20	250	263	142	60	110	101.6			18	26			Fig. 3	9.3		

*APMX : 6mm (GM, SM, GHプレーカ), 5mm (GLプレーカ), 3mm (Wプレーカ)

推奨切削条件 **M28**

● : 標準在庫
受 : 受注生産