

製品情報

対象被削材





技術資料 >> 1995

ISO13399記号 >> 1966

マークの見方 >> 670

エンドミル選定目安表 >> 688



●標準在庫 単位:mm

呼び記号	DC	APMX	LF	DCON	刃数	在庫	図番
VAMFPRD0500	5	15	80	6	4	●	1
VAMFPRD0600	6	17	80	6	4	●	2
VAMFPRD0700	7	22	80	8	4	●	1
VAMFPRD0800	8	28	85	8	4	●	2
VAMFPRD0900	9	28	95	10	4	●	1
VAMFPRD1000	10	34	100	10	4	●	2
VAMFPRD1200	12	40	110	12	4	●	2
VAMFPRD1400	14	40	110	12	4	●	3
VAMFPRD1500	15	40	120	16	4	●	1
VAMFPRD1600	16	48	125	16	4	●	2
VAMFPRD1800	18	48	125	16	4	●	3
VAMFPRD2000	20	57	145	20	4	●	2
VAMFPRD2200	22	57	145	20	5	●	3
VAMFPRD2400	24	68	150	25	5	●	1
VAMFPRD2500	25	68	150	25	5	●	2
VAMFPRD2800	28	68	160	25	5	●	3
VAMFPRD3000	30	68	165	25	6	●	3
VAMFPRD3200	32	80	175	32	6	●	2
VAMFPRD3500	35	80	175	32	6	●	3
VAMFPRD4000	40	94	185	32	6	●	3
VAMFPRD4500	45	94	200	42	6	●	3
VAMFPRD5000	50	113	200	42	6	●	3