

被削材	P	鋼	コーティング				サーメット	超硬	寸法 (mm)					形状			
	M	ステンレス鋼	EP6120	VP15TF	VP20RT	UP20M	MP8010	NX2525	NX4545	UT120T	HT110	L	IC		S	BS	RE
被削材 P 鋼 M ステンレス鋼 K 鋳鉄 N 非鉄金属 S 耐熱合金、チタン合金 H 高硬度鋼	切削状態(目安): ●:安定切削 ●:一般切削 ✖:不安定切削		ホーニング: E:丸ホーニング F:シャープエッジ														
	対応カッタ インサート 外観	呼び記号	精度	ホーニング					寸法 (mm)					形状			
	TBE1	SPMT120408-A	M	E	●	●	●	●	●	●	●	—	12.7		4.76	—	0.8
	CESP CFSP CGSP S300 S400	SPMW090304	M	E*1	●	●	●	●	●	●	●	—	9.525	3.18	—	0.4	
		SPMW090308	M	E*1	●	●	●	●	●	●	●	—	9.525	3.18	—	0.8	
		SPMW120304	M	E*1	●	●	●	●	●	●	●	—	12.7	3.18	—	0.4	
SPMW120308		M	E*1	●	●	●	●	●	●	●	—	12.7	3.18	—	0.8		
SPX	SPMX120408-JM	M	E	●	●						—	12.7	4.80	—	0.8		
SPX	SPMX120408-WH	M	E	●	●						—	12.7	4.76	—	0.8		
SRF	* SRFT10	—	F	●	●		●				8.5	10	2.6	0.5	5		
	* SRFT12	—	F	●	●		●				10	12	3	0.5	6		
	* SRFT16	—	F	●	●		●				12	16	4	1	8		
	* SRFT20	—	F	●	●		●				15	20	5	1	10		
	* SRFT25	—	F	●	●		●				18.5	25	6	1	12.5		
	* SRFT30	—	F	●	●		●				22.5	30	7	1	15		
	* SRFT32	—	F	●	●		●				23.5	32	7	1	16		

* 1ケース2個入りです。

*1 NX2525、NX4545のホーニングは"1"です。

