



マジックドリルDRC用チップ

型番の表示方法(チップ)



チップ材種 PR0315

PR0315は強靱性超微粒子超硬にTiAlNコーティングされた、耐摩耗性・耐欠損性共に優れたチップ材種です。炭素鋼・合金鋼・鋳鉄等の幅広い被削材に適用し、安定加工を可能にします。

形状	型番	寸法 (mm)		PVDコーティング	適合ホルダ ● K29~K31, K34~K36
		DC	PL	PR0315	
 	DC 0794M-SC	7.94	1.37	●	SS10-DRC080M-○ SF12-DRC080M-○
	0800M-SC	8.00	1.38	●	
	0810M-SC	8.10	1.40	●	
	0820M-SC	8.20	1.42	●	
	0830M-SC	8.30	1.43	●	
	0840M-SC	8.40	1.45	●	
	DC 0850M-SC	8.50	1.47	●	SS10-DRC085M-○ SF12-DRC085M-○
	0860M-SC	8.60	1.48	●	
	0870M-SC	8.70	1.50	●	
	0880M-SC	8.80	1.52	●	
	0890M-SC	8.90	1.54	●	
	DC 0900M-SC	9.00	1.55	●	SS10-DRC090M-○ SF12-DRC090M-○
	0910M-SC	9.10	1.57	●	
	0920M-SC	9.20	1.59	●	
	0930M-SC	9.30	1.61	●	
	0940M-SC	9.40	1.62	●	
	DC 0950M-SC	9.50	1.64	●	SS10-DRC095M-○ SF12-DRC095M-○
	0960M-SC	9.60	1.66	●	
	0970M-SC	9.70	1.67	●	
	0980M-SC	9.80	1.69	●	
	0990M-SC	9.90	1.71	●	
	DC 1000M-SC	10.00	1.72	●	SS12-DRC100M-○ SF16-DRC100M-○
	1010M-SC	10.10	1.74	●	
	1020M-SC	10.20	1.76	●	
	1030M-SC	10.30	1.78	●	
	1040M-SC	10.40	1.80	●	
	DC 1050M-SC	10.50	1.81	●	SS12-DRC105M-○ SF16-DRC105M-○
	1060M-SC	10.60	1.83	●	
	1070M-SC	10.70	1.85	●	
	1080M-SC	10.80	1.86	●	
	1090M-SC	10.90	1.88	●	
	DC 1100M-SC	11.00	1.90	●	SS12-DRC110M-○ SF16-DRC110M-○
	1110M-SC	11.10	1.91	●	
	1120M-SC	11.20	1.93	●	
	1130M-SC	11.30	1.95	●	
	1140M-SC	11.40	1.97	●	
	DC 1150M-SC	11.50	1.98	●	SS12-DRC115M-○ SF16-DRC115M-○
	1160M-SC	11.60	2.00	●	
	1170M-SC	11.70	2.02	●	
	1180M-SC	11.80	2.04	●	
	1190M-SC	11.90	2.06	●	
	DC 1200M-SC	12.00	2.07	●	SS14-DRC120M-○ SF16-DRC120M-○
	1210M-SC	12.10	2.09	●	
	1220M-SC	12.20	2.11	●	
	1230M-SC	12.30	2.12	●	
	1240M-SC	12.40	2.14	●	

k8寸法公差

DC	k8(mm)
7.94 10.00	+0.022 0
10.10 18.00	+0.027 0
18.10 25.99	+0.033 0

k8はチップ自体の寸法公差です。
加工穴径の寸法公差ではありません。

チップの販売個数は、
1ケース1個入りです

●：標準在庫