


3V/3VX プーリ寸法表

図 1-9-2



3V/3VXプーリ寸法表

●3V/3VX-3溝 F=38

表1-15-2

(単位mm)

| 有効径 De | 外 径 Do | ピッチ径 Dp | 内 径 Di | ボス径 Db | 適応 プッシング | プーリ形状 | 基 準 寸 法 | | | | | | | | プッシュを除く | |
|-----------|-----------|------------|-----------|-----------|-------------|-------|---------|------|------|---|-------|------|----|-----|-------------|---|
| | | | | | | | OL | L | P | C | H | G | X | E | 質 量 (kg) | GD ² (kg・m ²) |
| 80 | 81 | 78.8 | 68 | - | H | 4 | 50.1 | 31.7 | 8.1 | - | 63.2 | 11.1 | 35 | 4 | 0.751 | 0.0037 |
| 90 | 91 | 88.8 | 80 | - | P1 | 4 | 56.4 | 49.2 | 12.9 | - | 76.2 | 15.9 | 35 | 5.5 | 0.914 | 0.0058 |
| 100 | 101 | 98.8 | 80 | - | P1 | 4 | 56.4 | 49.2 | 12.9 | - | 76.2 | 15.9 | 35 | 5.5 | 1.29 | 0.0094 |
| 112 | 113 | 110.8 | 80 | - | P1 | 4 | 56.4 | 49.2 | 12.9 | - | 76.2 | 15.9 | 35 | 5.5 | 1.81 | 0.015 |
| 125 | 126 | 123.8 | - | 120 | Q1 | 2 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 2.27 | 0.026 |
| 140 | 141 | 138.8 | - | 130 | Q1 | 2 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 3.18 | 0.042 |
| 150 | 151 | 148.8 | - | 130 | Q1 | 2 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 3.70 | 0.056 |
| 160 | 161 | 158.8 | - | 130 | Q1 | 2 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 4.42 | 0.071 |
| 180 | 181 | 178.8 | - | 130 | Q1 | 2 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 4.92 | 0.095 |
| 200 | 201 | 198.8 | 169 | 130 | Q1 | 5 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 5.42 | 0.125 |
| 250 | 251 | 248.8 | 219 | 130 | Q1 | 5 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 6.82 | 0.243 |
| 315 | 316 | 313.8 | 284 | 130 | Q1 | 5 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 7.98 | 0.472 |
| 400 | 401 | 398.8 | 369 | 130 | Q1 | 5 | 71.1 | 63.5 | 26.1 | - | 104.8 | 19.1 | 45 | 7 | 9.28 | 0.952 |
| 500 | 501 | 498.8 | 469 | 150 | R1 | 5 | 80.2 | 73 | 35.2 | - | 136.5 | 22.2 | 51 | 7 | 17.5 | 1.66 |
| (630) | 631 | 628.8 | 599 | 150 | R1 | 5 | 80.2 | 73 | 35.2 | - | 136.5 | 22.2 | 51 | 7 | 16.8 | 4.32 |

●3V/3VX-4溝 F=49

表1-15-3

| | | | | | | | | | | | | | | | | | |
|-------|-----|-------|-----|----|-----|----|----|------|------|------|----|-------|------|----|-----|-------|--------|
| 80 | 81 | 78.8 | 49 | 68 | - | H | 3 | 61.1 | 31.7 | 8.1 | 21 | 63.2 | 11.1 | 25 | 4 | 0.870 | 0.0049 |
| 90 | 91 | 88.8 | 59 | - | - | P1 | 6 | 70.4 | 49.2 | - | 15 | 76.2 | 15.9 | 34 | 5.5 | 1.15 | 0.0079 |
| 100 | 101 | 98.8 | 69 | - | - | P1 | 6 | 70.4 | 49.2 | - | 15 | 76.2 | 15.9 | 34 | 5.5 | 1.53 | 0.012 |
| 112 | 113 | 110.8 | 81 | - | - | P1 | 7 | 55.4 | 49.2 | 0.9 | - | 76.2 | 15.9 | 34 | 5.5 | 2.04 | 0.019 |
| 125 | 126 | 123.8 | - | - | - | Q1 | 1 | 75.1 | 63.5 | - | - | 104.8 | 19.1 | 49 | 7 | 2.42 | 0.030 |
| 140 | 141 | 138.8 | 109 | - | - | Q1 | 4 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 3.32 | 0.048 |
| 160 | 161 | 158.8 | 129 | - | - | Q1 | 4 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 4.80 | 0.083 |
| 180 | 181 | 178.8 | 149 | - | - | Q1 | 4 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 6.50 | 0.135 |
| 200 | 201 | 198.8 | 169 | - | 130 | Q1 | 14 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 5.92 | 0.151 |
| 250 | 251 | 248.8 | 219 | - | 130 | Q1 | 14 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 7.46 | 0.296 |
| 315 | 316 | 313.8 | 284 | - | 130 | Q1 | 14 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 8.81 | 0.582 |
| 400 | 401 | 398.8 | 369 | - | 130 | Q1 | 14 | 71.1 | 63.5 | 15.1 | - | 104.8 | 19.1 | 45 | 7 | 12.0 | 1.30 |
| 500 | 501 | 498.8 | 469 | - | 150 | R1 | 5 | 80.2 | 73 | 24.2 | - | 136.5 | 22.2 | 51 | 7 | 18.8 | 3.12 |
| (630) | 631 | 628.8 | 599 | - | 150 | R1 | 5 | 80.2 | 73 | 24.2 | - | 136.5 | 22.2 | 51 | 7 | 18.5 | 5.26 |

●()は非在庫品です。

