

SUS316L HEXAGON SOCKET HEAD CAP SCREWS


HEXAGON BOLTS

NUTS

WASHERS

SUS316L六角穴付ボルト/六角ボルト/ナット/座金

CADデータフォルダ名: 34_Screws



SUS316L六角穴付ボルト

型式		M×P	A	E	B	¥基準単価	¥スライド単価
Type	M-L					1~49本	50~200本
SSCB	3-6	3×0.5	5.5	3	2.5	120	84
	8					110	77
	10					110	77
	12					110	77
	15					120	84
	20					120	84
SSCB	4-8	4×0.7	7	4	3	120	84
	10					110	77
	12					110	77
	15					120	84
	20					120	84
	25					130	91
SSCB	5-8	5×0.8	8.5	5	4	120	84
	10					110	77
	12					110	77
	15					120	84
	20					120	84
	25					130	91
SSCB	6-10	6×1.0	10	6	5	110	77
	12					120	84
	15					120	84
	20					120	84
	25					130	91
	30					160	112
SSCB	8-15	8×1.25	13	8	6	150	105
	20					150	105
	25					160	112
	30					160	112
	35					200	140
	40					210	147
SSCB	10-20	10×1.5	16	10	8	220	154
	25					230	161
	30					250	175
	35					270	189
	40					290	203
	45					310	217
SSCB	12-20	12×1.75	18	12	10	320	224
	25						
	30						
	35						
	40						
	45						

SUS316L六角ボルト

型式		M×P	A	E	¥基準単価	¥スライド単価
Type	M-L				1~49本	50~200本
RSSCB	4-10	4×0.7	7	2.8	90	63
	12				90	63
	15				95	66
	20				95	66
	25				100	70
	30				110	77
RSSCB	5-10	5×0.8	8	3.5	90	63
	12				90	63
	15				95	66
	20				95	66
	25				100	70
	30				110	77
RSSCB	6-10	6×1.0	10	4.0	95	66
	12				95	66
	15				100	70
	20				100	70
	25				110	77
	30				125	88
RSSCB	8-15	8×1.25	13	5.5	130	91
	20				135	94
	25				140	98
	30				180	126
	35				190	133
	40				200	140
RSSCB	10-20	10×1.5	17	7.0	210	147
	25					
	30					
	35					
	40					
	45					

SUS316Lナット

型式		M	B	(e)	T	¥基準単価	¥スライド単価
Type						1~49コ	50~200コ
SSLBNR	3	5.5	6.4	2.4	70	49	
	4	7	8.1	3.2	70	49	
	5	8	9.2	4	75	53	
	6	10	11.5	5	80	56	
	8	13	15	6.5	90	63	
	10	17	19.6	8	110	77	
SSLBNR	12	19	21.9	10	140	98	

SUS316Lばね座金

型式		No.	d	D	t	¥基準単価	¥スライド単価
Type						1~49コ	50~200コ
SSSLW	3	3.1	5.9	0.7	60	39	
	4	4.1	7.6	1.0	60	39	
	5	5.1	9.2	1.3	65	42	
	6	6.1	12.2	1.5	65	42	
	8	8.2	15.4	2.0	70	46	
	10	10.2	18.4	2.5	80	52	
SSSLW	12	12.2	21.5	3.0	100	65	

SUS316L座金

型式		No.	D	d	t	¥基準単価	¥スライド単価
Type						1~49コ	50~200コ
SSPWF	3	7	3.2	0.5	60	39	
	4	9	4.3	0.8	60	39	
	5	10	5.3	1.0	65	42	
	6	12.5	6.4	1.5	65	42	
	8	17	8.4	1.5	75	49	
	10	21	10.5	2.0	90	59	
SSPWF	12	24	13.0	2.5	160	104	

Order
注文例

型式

SSCB5-12
SSSLW8Delivery
出荷日

在庫品 翌日出荷 P.133

ご希望によりPM6:00迄、当日出荷受付致します。

数量区分	標準対応	個別対応
小口	大口	
数量	1~200	201~
出荷日	通常	お見積り

表示数量超えはWOSにてご確認ください。

SUS316Lの特性

SUS316LはSUS304にMo(モリブデン)を添加したもので高い耐食性があります。

＜参考:ステンレス材耐食性＞


試験方法

複合腐食試験として JIS H 8502
サイクル試験方法に準拠

試験条件

- ①塩水噴霧試験(5%NaCl, 35℃) 2hr
- ②乾燥(60℃) 4hr
- ③湿潤(95%RH, 35℃) 2hr

8hrで1サイクル



試験開始前、48hr、168hrで試験片の外観