

旋削用インサート[ポジ]




TCMT 08 02 04

切れ刃長 厚さ コーナR
* 詳細はA002ページをご参照ください。

被削材別切りくず有効範囲

仕上げ切削... 軽切削... 中切削...



A 旋削用インサート

切削状態(目安): ●: 安定切削 ●: 一般切削 * : 不安定切削

被削材	呼び記号	RE (mm)	コーティング															サームット		コーテッドサームット				超硬合金			参照インデックス	対応ホルダ																						
			UE6105	UE6110	UE6020	MC6015	MC6025	UH6400	MS6015	MC7025	MP7035	US7020	US735	US905	MC5005	MC5015	UC5105	UC5115	MH5115	NEW	MP9005	MP9015	VP05RT	VP10RT	VP15TF	UP20M			NX2525	NX3035	MP3025	AP25N	VP25N	VP45N	UTi20T	HTi05T	HTi10	RT9010	MT9005	TF15										
Standard	TCMT080204	0.4																																																
	TCMT090204	0.4	●	▲							●																	●																						
	TCMT110202	0.2	●	▲							●																●																							
	TCMT110204	0.4	●	●	▲						●					●										●																								
	TCMT110208	0.8	●	●																						●																								
	TCMT130302	0.2	●																											●																				
	TCMT130304	0.4	●																																															
	TCMT16T304	0.4	●	●	▲						●															●																								
中切削	TCMT16T308	0.8	●	●	▲					●															●																									
	TCMT16T312	1.2	●																																															
	TCMW110204	0.4												●	●	●	●																																	
	TCMW130304	0.4												●	●	●	●																																	
	TCMW16T304	0.4												●	●	●	●																																	
Flat Top	TCMW16T308	0.8											●	●	●	●																																		
	TCMW16T312	1.2											●	●																																				
	TCGW110204	0.4																																																
	TCGW110208	0.8																																																
	TCGW110204E	0.4																																																
Flat Top	TCGW110208E	0.8																																																

● = NEW

●: 標準在庫品 ▲: 現在標準在庫品で将来新製品と置き換わる製品 (1ケース10個入りです)