



カス詰まり対策超硬ボタンダイ

一ツバ付タイプ	RoHS10	材質 硬度	シャンク径 D公差	型式	形状						
	RoHS10	V40 (HIP) 87~88HRA	D_{m5}	SV-WHD	 <table><tr><td>D</td><td>3~5</td><td>6~10</td></tr><tr><td>R</td><td>R≤0.2</td><td>R≤0.5</td></tr></table>	D	3~5	6~10	R	R≤0.2	R≤0.5
			D	3~5		6~10					
R	R≤0.2	R≤0.5									
$D^{+0.005}_0$	SVA-WHD										
シャンク径公差Dは $m5^{+0.005}_0$ 選択					① () 寸法は参考値となります。						

一ストレートタイプ	RoHS10	材質 硬度	シャンク径 D公差	型式	形状						
	RoHS10	V40 (HIP) 87~88HRA	D_{n5}	SV-WSD	 <table><tr><td>D</td><td>3~5</td><td>6~10</td></tr><tr><td>R</td><td>R≤0.2</td><td>R≤0.5</td></tr></table>	D	3~5	6~10	R	R≤0.2	R≤0.5
			D	3~5		6~10					
R	R≤0.2	R≤0.5									
$D^{+0.005}_0$	SVA-WSD										
シャンク径公差Dは $n5^{+0.005}_0$ 選択					① () 寸法は参考値となります。						

D公差			型式		L	指定0.01mm単位 min. P max.		V	G	d	H	T
D	m5	n5	Type	D								
3	$+0.006$ $+0.002$	$+0.008$ $+0.004$	ツバ付タイプ (D_{m5}) SV-WHD	ストレートタイプ (D_{n5}) SV-WSD	3	0.50~1.00	0.4	0.2		1.4	4	3
4					4	0.50~1.50				2.0	5	
5	$+0.009$ $+0.004$	$+0.013$ $+0.008$			5	0.50~2.50				3.0	6	
6					6	1.00~3.00	0.8	0.3		3.4	9	5
8	$+0.012$ $+0.006$	$+0.016$ $+0.010$	($D^{+0.005}_0$) SVA-WHD	($D^{+0.005}_0$) SVA-WSD	8	1.00~4.00				4.4	11	
10					10	2.00~6.00				6.4	13	

Order
注文例
 型式 — L — P
 SV-WHD10 — 25 — P4.50
Delivery
出荷日

3 日日出荷