


# MC6100シリーズ

## ネガティブインサート(穴つき)

M級精度



(mm)

呼び記号	切削領域	NEW			IC	S	RE	D1
		MC6115	MC6125	MC6135				
CNMG120404-MH	M	●	●	○	12.7	4.76	0.4	5.16
CNMG120408-MH	M	●	●	●	12.7	4.76	0.8	5.16
CNMG120412-MH	M	●	●	●	12.7	4.76	1.2	5.16
CNMG120416-MH	M	●	●	○	12.7	4.76	1.6	5.16
CNMG160608-MH	M	●	●	○	15.875	6.35	0.8	6.35
CNMG160612-MH	M	●	●	●	15.875	6.35	1.2	6.35
CNMG160616-MH	M	●	●	○	15.875	6.35	1.6	6.35
CNMG190612-MH	M	●	●	●	19.05	6.35	1.2	7.93
CNMG190616-MH	M	●	●	○	19.05	6.35	1.6	7.93
CNMG090308	M	●	○	○	9.525	3.18	0.8	3.81
CNMG09T304	M	●	○	○	9.525	3.97	0.4	3.81
CNMG09T308	M	●	○	○	9.525	3.97	0.8	3.81
CNMG120404	M	●	●	●	12.7	4.76	0.4	5.16
CNMG120408	M	●	●	●	12.7	4.76	0.8	5.16
CNMG120412	M	●	●	●	12.7	4.76	1.2	5.16
CNMG120416	M	●	●	○	12.7	4.76	1.6	5.16
CNMG160608	M	●	●	●	15.875	6.35	0.8	6.35
CNMG160612	M	●	●	●	15.875	6.35	1.2	6.35
CNMG160616	M	●	●	○	15.875	6.35	1.6	6.35
CNMG190608	M	●	●	●	19.05	6.35	0.8	7.93
CNMG190612	M	●	●	●	19.05	6.35	1.2	7.93
CNMG190616	M	●	●	○	19.05	6.35	1.6	7.93
CNMG120408-MW	M	●	●	●	12.7	4.76	0.8	5.16
CNMG120412-MW	M	●	●	●	12.7	4.76	1.2	5.16
CNMG120408-RP	R	●	●	●	12.7	4.76	0.8	5.16
CNMG120412-RP	R	●	●	●	12.7	4.76	1.2	5.16
CNMG120416-RP	R	●	●	○	12.7	4.76	1.6	5.16
CNMG160612-RP	R	●	●	●	15.875	6.35	1.2	6.35
CNMG160616-RP	R	●	●	○	15.875	6.35	1.6	6.35
CNMG190612-RP	R	●	●	●	19.05	6.35	1.2	7.93
CNMG190616-RP	R	●	●	○	19.05	6.35	1.6	7.93
CNMG120408-GH	R	●	●	○	12.7	4.76	0.8	5.16
CNMG120412-GH	R	●	●	○	12.7	4.76	1.2	5.16
CNMG120416-GH	R	●	●	○	12.7	4.76	1.6	5.16
CNMG160612-GH	R	●	●	○	15.875	6.35	1.2	6.35
CNMG160616-GH	R	●	●	○	15.875	6.35	1.6	6.35
CNMG190612-GH	R	●	●	○	19.05	6.35	1.2	7.93
CNMG190616-GH	R	●	●	○	19.05	6.35	1.6	7.93

呼び記号	切削領域	NEW			IC	S	RE	D1
		MC6115	MC6125	MC6135				
CNMM120408-HX	H	○	○	●	12.7	4.76	0.8	5.16
CNMM120412-HX	H	○	○	●	12.7	4.76	1.2	5.16
CNMM160612-HX	H	○	○	●	15.875	6.35	1.2	6.35
CNMM160616-HX	H	○	○	●	15.875	6.35	1.6	6.35
CNMM190612-HX	H	●	○	●	19.05	6.35	1.2	7.93
CNMM190616-HX	H	●	○	●	19.05	6.35	1.6	7.93
CNMM190624-HX	H	●	○	●	19.05	6.35	2.4	7.93
CNMM250924-HX	H	●	○	○	25.4	9.52	2.4	9.12
CNMM120408-HL	H	○	○	●	12.7	4.76	0.8	5.16
CNMM120412-HL	H	○	○	●	12.7	4.76	1.2	5.16
CNMM120416-HL	H	○	○	●	12.7	4.76	1.6	5.16
CNMM160612-HL	H	○	○	●	15.875	6.35	1.2	6.35
CNMM160616-HL	H	○	○	●	15.875	6.35	1.6	6.35
CNMM190612-HL	H	○	○	●	19.05	6.35	1.2	7.93
CNMM190616-HL	H	○	○	●	19.05	6.35	1.6	7.93
CNMM190624-HL	H	○	○	●	19.05	6.35	2.4	7.93
CNMM250924-HR	H	○	○	○	25.4	9.52	2.4	9.12
CNMM190616-HV	H	○	○	●	19.05	6.35	1.6	7.93
CNMM190624-HV	H	○	○	●	19.05	6.35	2.4	7.93
CNMM250924-HV	H	○	○	○	25.4	9.52	2.4	9.12
CNMM120408-HZ	H	○	○	●	12.7	4.76	0.8	5.16
CNMM120412-HZ	H	○	○	●	12.7	4.76	1.2	5.16
CNMM120416-HZ	H	○	○	●	12.7	4.76	1.6	5.16
CNMM160612-HZ	H	○	○	○	15.875	6.35	1.2	6.35
CNMM160616-HZ	H	○	○	○	15.875	6.35	1.6	6.35
CNMM190612-HZ	H	○	○	○	19.05	6.35	1.2	7.93
CNMM190616-HZ	H	○	○	○	19.05	6.35	1.6	7.93
CNMM160612-HM	H	○	○	○	15.875	6.35	1.2	6.35
CNMM160616-HM	H	○	○	○	15.875	6.35	1.6	6.35
CNMM190612-HM	H	○	○	○	19.05	6.35	1.2	7.93
CNMM190616-HM	H	○	○	○	19.05	6.35	1.6	7.93
CNMM190624-HM	H	○	○	○	19.05	6.35	2.4	7.93
CNMM250924-HM	H	○	○	○	25.4	9.52	2.4	9.12

● = NEW

●: 標準在庫品 ○: 近日発売

(インサートは、1ケース 10個入りです)