


ストッパ

抜け止めや可変範囲のストッパとして

USQ-500




材質:SUS 304

品番	□ A	B	H	C	W	締付ネジ	本体価格
USQ 10-500	□10	13	10	10	20	M4	3,900
USQ 12-500	□12	16					4,000
USQ 13-500	□13						4,200
USQ 16-500	□16	19	13	12	25	M5	4,500
USQ 19-500	□19	21	15		30		5,400
USQ 20-500	□20						5,400

角・ネジタイプ

部品の取付けに使用。2個使用で自在に取付け

USQ-503~506




材質:SUS 304

品番	☐ A	B	H	C	W	M	締付ネジ	本体価格
USQ 10-503	☐ 10	13	15	10	20	M3	M4	4,000
USQ 10-504						M4		4,000
USQ 12-503	☐ 12	16	14			M3		4,200
USQ 12-504						M4		4,200
USQ 13-503	☐ 13		16	12	25	M3	M5	4,400
USQ 13-504						M4		4,400
USQ 16-504	☐ 16	19	20			M4		4,800
USQ 16-505								M5
USQ 19-505	☐ 19	21	25		30	M5	5,600	
USQ 19-506						M6	5,700	
USQ 20-505	☐ 20					M5	5,700	
USQ 20-506						M6	5,700	

角・ネジタイプ (直角方向)

2個のネジ(軸に直角)でボードや機能器具取付けに

USQ-223~226




材質:SUS 304

品番	□ A	φ D	E	B	G	2-M	締付ネジ	本体価格
USQ 10-223	□10	φ 19	14.5	16.5	8	2-M3	M4	4,200
USQ 10-224						2-M4		4,200
USQ 12-223	□12	φ 22	15.5	17.5	12	2-M3	M4	4,500
USQ 12-224						2-M4		4,500
USQ 13-223	□13				13	2-M3	M4	4,500
USQ 13-224						2-M4		4,500
USQ 16-224	□16	φ 25	19	21		2-M4	M5	5,100
USQ 16-225						2-M5		5,100
USQ 19-225	□19	φ 29	21.5	25	15	2-M5	M5	6,500
USQ 19-226						2-M6		6,500
USQ 20-225	□20					2-M5	M5	6,500
USQ 20-226						2-M6		6,500

角・ネジタイプ (平行方向)

2個のネジ(軸に平行)でボードや機能器具取付けに

USQ-233~236



材質:SUS 304

品番	□ A	φ D	E	B	G	2-M	締付ネジ	本体価格
USQ 10-233	□10	φ 19	14.5	16.5	8	2-M3	M4	4,200
USQ 10-234						2-M4		4,200
USQ 12-233	□12	φ 22	15.5	17.5	12	2-M3	M4	4,500
USQ 12-234						2-M4		4,500
USQ 13-233	□13				13	2-M3	M4	4,500
USQ 13-234						2-M4		4,500
USQ 16-234	□16	φ 25	19	21		2-M4	M5	5,100
USQ 16-235						2-M5		5,100
USQ 19-235	□19	φ 29	21.5	25	15	2-M5	M5	6,500
USQ 19-236						2-M6		6,500
USQ 20-235	□20					2-M5	M5	6,500
USQ 20-236						2-M6		6,500