


M-1 標準Vプーリー - M適用

選定ナビ



CAD Download



単位: mm

品番	価格 (円)	ピッチ円直径 d_p	外径 d_e	最大軸穴径 d	下穴径 d	形状 図番	ハブ				リム		慣性モーメント ($\text{kg} \cdot \text{m}^2$)	質量 (kg)
							d_b	l	s_1	s_2	w	h^{+2}_0		
2-M-1	450	45.4	50.8	16	—	11U	28	30	13	—	17	—	0.000059	0.26
2 ½-M-1	630	58.1	63.5	17	—	10U	30	30	13	—	17	—	0.000129	0.34
3-M-1	730	70.8	76.2	17	—	10U	30	30	13	—	17	—	0.000248	0.42
3 ½-M-1	840	83.5	88.9	18	—	10U	32	30	13	—	17	—	0.000442	0.53
4-M-1	970	96.2	101.6	18	—	10S	32	30	13	—	17	13.5	0.000704	0.57
4 ½-M-1	1,200	108.9	114.3	18	—	10S	32	30	13	—	17	13.5	0.00105	0.63
5-M-1	1,430	121.6	127	18	—	10S	32	30	13	—	17	13.5	0.00151	0.7
5 ½-M-1	1,490	134.3	139.7	18	—	10S	32	30	13	—	17	13.5	0.00207	0.77
6-M-1	1,520	147	152.4	19	—	10S	35	30	13	—	17	13.5	0.00286	0.92
7-M-1	1,740	172.4	177.8	21	—	10S	38	30	13	—	17	13.5	0.00468	1.06
8-M-1	1,980	197.8	203.2	21	—	10S	38	30	13	—	17	13.5	0.00722	1.19

追加サービスをご利用ください。

Vプーリーに軸穴・キー溝・押しねじ穴の
追加加工をいたします。実働1日出荷。

→ P.304



● 軸穴・キー溝・押しねじ追加加工 → P.304

対応可・別料金

● 品番指定



直送



14時当日出荷



NBK ネットショップ

3-M-1

