


B-1 標準Vプーリー - B・BX適用

WEB 選定ナビ WEB CAD Download



単位:mm

品番 ①	価格 (円)	ピッチ円直径 d_p	外径 d_e	最大軸穴径 d	下穴径 d	形状 図番	ハブ d_b	l	s_1	s_2	リム w	h^{+2}_0	慣性モーメント (kg·m ²)	質量 (kg)
2 ½-B-1	670	52.5	63.5	19	—	11U	42	43	19	—	24	—	0.000192	0.57
3-B-1	730	65.2	76.2	24	—	21U	44	25	19	18	24	18	0.000349	0.61
3 ½-B-1	880	77.9	88.9	24	—	21U	44	25	19	18	24	18	0.0006	0.73
4-B-1	1,180	90.6	101.6	28	—	21U	50	28	19	15	24	18	0.00105	1.01
4 ½-B-1	1,460	103.3	114.3	28	—	23U	50	30	15	9	24	18	0.00157	1.15
5-B-1	1,770	116	127	28	—	23U	50	30	15	9	24	18	0.0023	1.3
5 ½-B-1	1,890	128.7	139.7	28	—	23U	50	30	15	9	24	18	0.00325	1.47
6-B-1	2,120	141.4	152.4	28	—	23U	50	30	15	9	24	18	0.00448	1.64
6 ½-B-1	2,170	154.1	165.1	31	—	20X	56	30	8	2	24	18	0.00533	1.64
7-B-1	2,250	166.8	177.8	33	—	10X	60	30	6	—	24	18	0.00699	1.87
8-B-1	2,490	192.2	203.2	33	—	10X	60	30	6	—	24	18	0.011	2.16
9-B-1	2,730	217.6	228.6	33	—	10X	60	30	6	—	24	18	0.0164	2.44
10-B-1	3,350	243	254	36	—	10X	64	34	10	—	24	18	0.0233	2.88
11-B-1	3,620	268.4	279.4	36	—	10X	64	34	10	—	24	18	0.0318	3.17
12-B-1	4,150	293.8	304.8	36	—	10X	64	34	10	—	24	18	0.0421	3.43
13-B-1	4,870	319.2	330.2	36	—	10X	64	38	14	—	24	18	0.0563	3.96
14-B-1	5,570	344.6	355.6	39	—	10X	70	40	16	—	24	18	0.0715	4.45
15-B-1	6,340	370	381	41	—	10X	74	40	16	—	24	18	0.0893	4.85
16-B-1	6,850	395.4	406.4	41	—	10X	74	40	16	—	24	18	0.11	5.17

追加工サービスをご利用ください。

Vプーリーに軸穴・キー溝・押しねじ穴の追加工をいたします。実働1日目出荷。

→ P.304



● 軸穴・キー溝・押しねじ追加工 → P.304
対応可・別料金

● 品番指定

直送



14時当日出荷

NBKネットショップ

4 ½-B-1

