


XHS-C フレキシブルカップリング - シングルディスクタイプ

WEB 選定ナビ WEB CAD Download 0 パックラッシュ0 高トルク 高剛性

XHS-C



外径φ15

寸法・価格

単位: mm

品番	価格(円)	A	L	W	F	G	M	ねじ締めつけトルク (N・m)
XHS-15C	3,660	15	7.5	15.9	2.1	5	M2	0.45
XHS-19C	2,910	19	9.2	19.3	2.6	7	M2	0.5
XHS-25C	3,120	25	11	23.1	3.3	9.25	M2.5	1
XHS-27C	3,140	27	11	23.1	3.3	10.25	M2.5	1
XHS-34C	3,540	34	12.5	26.4	3.75	13	M3	1.5
XHS-39C	4,030	39	15.5	32.8	4.5	14.5	M4	3.5
XHS-44C	5,050	44	15.5	32.8	4.5	17	M4	3.5
XHS-56C	6,020	56	20.5	43.5	6	21	M5	8
XHS-64C	7,520	64	24	51.2	7	24	M6	13
XHS-79C	12,600	79	30	63.6	8.75	29	M8	28
XHS-98C	19,600	98	32	69	8.7	38	M8	28

品番	標準軸穴径 D1・D2																												
	3	4	5	6	6.35	8	9.525	10	11	12	14	15	16	17	18	19	20	22	24	25	28	30	32	35	38	40	42	45	50
XHS-15C	●	●	●	●																									
XHS-19C	●	●	●	●	●	●																							
XHS-25C		●	●	●	●	●	●	●	●	●																			
XHS-27C		●	●	●	●	●	●	●	●	●	●																		
XHS-34C			●	●	●	●	●	●	●	●	●	●	●																
XHS-39C				●	●	●	●	●	●	●	●	●	●	●	●	●	●												
XHS-44C						●	●	●	●	●	●	●	●	●	●	●	●	●											
XHS-56C						●	●	●	●	●	●	●	●	●	●	●	●	●	●	●									
XHS-64C								●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
XHS-79C										●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
XHS-98C																					●	●	●	●	●	●	●	●	●

- 全商品に六角穴付きボルトが付属しています。
- 適用軸径の推奨寸法許容差はh6およびh7です。(φ35のみ軸径の推奨寸法許容差は、-0.025~+0.010になります。)

⚠ 使用上の注意

- Dカット軸に取りつける場合は、軸のDカット面の位置に注意してください。
→ P.292
- カップリングの外径から六角穴付きボルトが飛び出して、回転直径が外径より大きくなるサイズがあります。カップリングの干渉に注意してください。
→ P.289

軸穴・キー溝追加加工 → P.2139 クリーン洗浄・クリーン梱包 → P.2145 ステンレスねじ変更 → P.2143
 対応可・別料金 お問い合わせください お問い合わせください