



フェルール

■シングルタイプ

RoHS10
P2をご確認ください



■材質 端子部：銅スリーブ（すずめっき付）／絶縁体：ポリプロピレン ■規格 ○：DIN 46228/4 準拠品

品番	各部の寸法 mm				適用電線サイズ		適用工具 手動工具	色	包装個数
	φF	φD	ℓ	L	撚線mm ²	AWG			
NF 0.14-8	0.8	1.9	8.0	12.0	0.14	26	NH 89	灰	500
NF 0.25-6			6.0	10.0					
NF 0.25-8			8.0	12.0					
NF 0.25-10			10.0	14.0					
NF 0.25-12			12.0	16.0					
NF 0.34-6	0.8	1.9	6.0	10.0	0.3・0.34	22	ターコイズ(青緑)		
NF 0.34-8			8.0	12.0					
NF 0.34-10			10.0	14.0					
NF 0.34-12			12.0	16.0					
NF 0.5-6 ○	1.1	2.4	6.0	12.0	0.5	20	白		
NF 0.5-8 ○			8.0	14.0					
NF 0.5-10 ○			10.0	16.0					
NF 0.5-12			12.0	18.0					
NF 0.75-6 ○	1.3	2.7	6.0	12.0	0.5・0.75	20-18	灰		
NF 0.75-8 ○			8.0	14.0					
NF 0.75-10 ○			10.0	16.0					
NF 0.75-12 ○			12.0	18.0					
NF 1.0-6 ○	1.5	2.9	6.0	12.0	1.0	18	赤		
NF 1.0-8 ○			8.0	14.0					
NF 1.0-10 ○			10.0	16.0					
NF 1.0-12 ○			12.0	18.0					
NF 1.5-6 ○	1.8	3.3	6.0	12.0	1.25・1.5	16	黒		
NF 1.5-8 ○			8.0	14.0					
NF 1.5-10 ○			10.0	16.0					
NF 1.5-12 ○			12.0	18.0					
NF 2.08-8	2.05	3.5	8.0	14.0	2.0	14	黄		
NF 2.5-8 ○			8.0	15.0					
NF 2.5-10 ○			10.0	17.0					
NF 2.5-12 ○	2.3	4.1	12.0	19.0	2.0・2.5	14	青		
NF 4.0-10 ○			10.0	17.0					
NF 4.0-12 ○	2.9	4.7	12.0	19.0	3.5・4.0	12	橙/灰		
NF 6.0-12 ○			12.0	20.0					
NF 6.0-18 ○	3.6	6.1	18.0	26.0	5.5・6.0	10	黄/緑		
NF 10.0-12 ○			12.0	21.0					
NF 10.0-18 ○	4.6	7.4	18.0	27.0	10.0	8	NH 89	黄	
NF 10.0-18 ○			18.0	27.0					

D