





バイト

形状	呼び記号	勝手	在庫						寸法 (mm)								チップ呼び記号
			P		M	K		シャンク部				チップ部					
			ST10	ST120	ST140T	UT120T	HT105T	HT110	HT120	W	H	L	E	A	B	C	
31形(右勝手) 斜剣バイト 32形(左勝手) 斜剣バイト  <p>本図は右勝手(31形)を示す。</p>	31-0	右	●		●				10	10	80	2.7	10	6	3	0.3	01-0
	32-0	左		●					10	10	80	2.7	10	6	3	0.3	01-0
	31-1	右	●		●		●		13	13	100	4	13	9	3	0.5	01-1
	32-1	左		●		●		●	13	13	100	4	13	9	3	0.5	01-1
	31-2	右	●		●		●		16	16	120	4.5	16	11	4	0.5	01-2
	32-2	左		●		●		●	16	16	120	4.5	16	11	4	0.5	01-2
	31-3	右	●	●		●	●	●	19	19	140	5.5	19	13	5	0.5	01-3
	32-3	左		●		●			19	19	140	5.5	19	13	5	0.5	01-3
	31-4	右	●	●		●	●		25	25	160	6.5	22	15	6	1	01-4
	32-4	左		●	●	●		●	25	25	160	6.5	22	15	6	1	01-4
33形(右勝手) 片刃バイト 34形(左勝手) 片刃バイト  <p>0番の場合</p> <p>本図は右勝手(33形)を示す。</p>	33-0	右	●	●		●	●	●	10	10	80	—	10	6	3	0.3	04-0
	34-0	左	●	●		●	●	●	10	10	80	—	10	6	3	0.3	04-0
	33-1	右	●	●	●	●	●	●	13	13	100	4	13	9	3	0.5	04-1
	34-1	左	●	●		●	●	●	13	13	100	4	13	9	3	0.5	04-1
	33-2	右	●	●	●	●	●	●	16	16	120	4	16	11	4	0.5	04-2
	34-2	左	●	●		●	●	●	16	16	120	4	16	11	4	0.5	04-2
	33-3	右	●	●	●	●	●	●	19	19	140	5	19	13	5	0.5	04-3
	34-3	左	●	●	●	●	●	●	19	19	140	5	19	13	5	0.5	04-3
	33-4	右	●	●	●	●	●	●	25	25	160	5	22	15	6	1	04-4
	34-4	左	●	●	●	●	●	●	25	25	160	5	22	15	6	1	04-4
35形 真剣バイト  <p>両側</p>	35-0	—	●	●		●	●	●	10	10	80	—	10	10	3	0.3	07-0
	35-1	—	●	●		●	●	●	13	13	100	—	13	13	3	0.5	07-1
	35-2	—	●	●		●	●	●	16	16	120	—	16	16	4	0.5	07-2
	35-3	—	●	●		●	●	●	19	19	140	—	19	19	5	0.5	07-3
	35-4	—	●	●		●	●	●	25	25	160	—	25	20	6	1	07-4
	35-5	—	●	●		●	●	●	30	30	200	—	30	30	8	1	07-5
36形 先丸剣バイト  <p>両側</p>	36-0	—	●	●		●	●	●	10	10	80	—	10	10	3	2	06-0
	36-1	—	●	●		●	●	●	13	13	100	—	13	13	3	2.5	06-1
	36-2	—	●	●		●	●	●	16	16	120	—	16	16	4	3	06-2
	36-3	—	●	●	●	●	●	●	19	19	140	—	19	19	5	4	06-3
	36-4	—	●	●	●	●	●	●	25	25	160	—	22	22	6	4	06-4
	36-5	—	●	●		●	●	●	25	30	180	—	25	25	7	5	06-5
	36-6	—	●	●		●	●	●	30	35	200	—	30	30	8	6	06-6

●：標準在庫品