


- 生材から型鋼までの深穴加工に最適です。
- 7D ノンステップ加工が安定して可能です。

Stable cutting for 7D non-step drilling.



新商品

LIST 6538

オーダ方法 商品記号

単位 (Unit) : mm

商品記号 Code	直径 Dc	全長 L	溝長 ℓ	在庫 Stock	参考価格(円) Price (¥)
AGPSLSD1.0	1.0	48	26		1,470
AGPSLSD1.1	1.1	50	28		1,720
AGPSLSD1.2	1.2				1,620
AGPSLSD1.3	1.3	52	30		1,720
AGPSLSD1.4	1.4				1,720
AGPSLSD1.5	1.5	55	33		1,650
AGPSLSD1.6	1.6				1,770
AGPSLSD1.7	1.7	58	35		1,940
AGPSLSD1.8	1.8				1,840
AGPSLSD1.9	1.9	62	38		1,840
AGPSLSD2.0	2.0				1,520
AGPSLSD2.1	2.1	66	41		2,200
AGPSLSD2.2	2.2				2,200
AGPSLSD2.3	2.3	70	44		2,000
AGPSLSD2.4	2.4				2,200
AGPSLSD2.5	2.5	74	47		2,000
AGPSLSD2.6	2.6				2,000
AGPSLSD2.7	2.7				2,000
AGPSLSD2.8	2.8				2,120
AGPSLSD2.9	2.9	79	51		2,000
AGPSLSD3.0	3.0				2,000
AGPSLSD3.1	3.1				2,390
AGPSLSD3.2	3.2				2,390
AGPSLSD3.3	3.3	84	55		2,390
AGPSLSD3.4	3.4				2,390
AGPSLSD3.5	3.5				2,390
AGPSLSD3.6	3.6	91	60		2,650
AGPSLSD3.7	3.7				2,650
AGPSLSD3.8	3.8				2,650
AGPSLSD3.9	3.9				2,650
AGPSLSD4.0	4.0	96	64		2,650
AGPSLSD4.1	4.1				2,960
AGPSLSD4.2	4.2				2,960
AGPSLSD4.3	4.3				2,960
AGPSLSD4.4	4.4				2,960
AGPSLSD4.5	4.5	102	69		2,960
AGPSLSD4.6	4.6				3,350
AGPSLSD4.7	4.7				3,350
AGPSLSD4.8	4.8				3,350
AGPSLSD4.9	4.9				3,350
AGPSLSD5.0	5.0				3,350
AGPSLSD5.1	5.1	108	74		4,340
AGPSLSD5.2	5.2				4,340
AGPSLSD5.3	5.3				4,340
AGPSLSD5.4	5.4				4,340
AGPSLSD5.5	5.5				4,340
AGPSLSD5.6	5.6				4,380
AGPSLSD5.7	5.7	116	80		4,380
AGPSLSD5.8	5.8				4,380
AGPSLSD5.9	5.9				4,380
AGPSLSD6.0	6.0				4,380
AGPSLSD6.1	6.1				5,210
AGPSLSD6.2	6.2				5,210
AGPSLSD6.3	6.3				5,210
AGPSLSD6.4	6.4	124	86		5,210
AGPSLSD6.5	6.5				5,210
AGPSLSD6.6	6.6				5,400
AGPSLSD6.7	6.7				5,400
AGPSLSD6.8	6.8				5,400
AGPSLSD6.9	6.9	133	93		5,400

商品記号 Code	直径 Dc	全長 L	溝長 ℓ	在庫 Stock	参考価格(円) Price (¥)
AGPSLSD7.0	7.0				5,400
AGPSLSD7.1	7.1				5,750
AGPSLSD7.2	7.2				5,750
AGPSLSD7.3	7.3	133	93		5,750
AGPSLSD7.4	7.4				5,750
AGPSLSD7.5	7.5				5,750
AGPSLSD7.6	7.6				6,120
AGPSLSD7.7	7.7				6,120
AGPSLSD7.8	7.8				6,120
AGPSLSD7.9	7.9				6,120
AGPSLSD8.0	8.0				6,120
AGPSLSD8.1	8.1	142	100		6,770
AGPSLSD8.2	8.2				6,770
AGPSLSD8.3	8.3				6,770
AGPSLSD8.4	8.4				6,770
AGPSLSD8.5	8.5				6,770
AGPSLSD8.6	8.6				7,090
AGPSLSD8.7	8.7				7,090
AGPSLSD8.8	8.8				7,090
AGPSLSD8.9	8.9				7,090
AGPSLSD9.0	9.0				7,090
AGPSLSD9.1	9.1	151	107		8,210
AGPSLSD9.2	9.2				8,210
AGPSLSD9.3	9.3				8,210
AGPSLSD9.4	9.4				8,210
AGPSLSD9.5	9.5				8,210
AGPSLSD9.6	9.6				9,160
AGPSLSD9.7	9.7				9,160
AGPSLSD9.8	9.8				9,160
AGPSLSD9.9	9.9	162	116		10,100
AGPSLSD10.0	10.0				9,160
AGPSLSD10.5	10.5				12,100
AGPSLSD11.0	11.0				12,900
AGPSLSD11.5	11.5	173	125		14,200
AGPSLSD12.0	12.0				15,400
AGPSLSD12.5	12.5	184	134		20,000
AGPSLSD13.0	13.0				21,300

超硬ドリル

ハイスドリル

タップ

超硬
エンドミル

ハイス
エンドミル

切断工具

バック・
セット商品
その他

精密工具

技術資料
索引

一般 構造用鋼	炭素鋼	合金鋼 調質鋼	ダイス鋼 プレハードン鋼	高硬度鋼	
SS400	S45C S50C	SCM NAK	30 ~ 40 HRC	40 ~ 50 HRC	50 ~ 65 HRC
—	◎	◎	◎	×	×
ステンレス鋼		Ti 合金 耐熱合金	鋳鉄	アルミ合金	銅合金
SUS304 SUS316	SUS420	Ti / Ni Alloy	FC / FCD	AC / ADC	Cu
×	—	—	◎	—	—

◎:最適 Excellent ○:適用 Good ×:不適 Not Used —:推奨しません Not recommended