


●もっとも広い用途で使用される汎用ドリルです。

This drill having long flute is general drills for deep holes.



LIST 650

オーダー方法 LTD 直径 × 全長

(□商品: LTD 直径 × 全長 × 溝長)

(*印商品: LTD 直径 × 全長 × 溝長 × MT シャンク)

直径4.0~6.9
在庫品限り

単位 (Unit) : mm

直径 Dc	全長 L	溝長 ℓ	シャンク MT No.	在庫 Stock	参考価格(円) Price (¥)	直径 Dc	全長 L	溝長 ℓ	シャンク MT No.	在庫 Stock	参考価格(円) Price (¥)
4.0	200	120			-	7.5	375				-
4.0	250	150			-	7.5	400	250			-
4.0	300	200			-	7.5	400	275			-
4.1	200				-	7.6	250				-
4.2	200				-	7.7	250	150		□	-
4.3	200				-	7.8	250				-
4.4	200				-	7.9	250				-
4.5	200	120			-	8.0	200	100			-
4.6	200				-	8.0	225	125			-
4.7	200				-	8.0	250	150		●	11,000
4.8	200				-	8.0	275	175		□	-
4.9	200				-	8.0	300	200		●	14,000
5.0	250	150			-	8.0	325			□	-
5.0	300	200			-	8.0	350	225		●	19,000
5.0	350	225			-	8.0	375	250			-
5.1	250				-	8.0	400				-
5.2	250				-	8.0	400	275			-
5.3	250				-	8.0	450	300			-
5.4	250				-	8.0	500	325			-
5.5	250	150		□	-	8.0	500	350			-
5.6	250				-	8.0	600				-
5.7	250				-	8.0	600	400			-
5.8	250				-	8.0	700				-
5.9	250				-	8.0	700	450			-
6.0	250				-	8.0	800	500		□	-
6.0	300	200			-	8.1	250	150			-
6.1	250				-	8.1	300	200			-
6.2	250				-	8.2	250	150			-
6.3	250	150			-	8.2	300	200			-
6.4	250				-	8.2	350	250			-
6.5	250		1		-	8.3	250	150			-
6.5	300	200			-	8.3	300	200			-
6.5	350	225			-	8.4	250	150			-
6.6	250				-	8.4	300	200			-
6.7	250	150			-	8.5	200	100			-
6.7	300	200			-	8.5	225	125			-
6.8	250				-	8.5	250	150		●	10,800
6.8	300	200			-	8.5	275	175		□	-
6.9	250	150			-	8.5	300	200		●	13,800
7.0	200	100			-	8.5	325			□	-
7.0	225	125			-	8.5	350	225		●	18,400
7.0	250	150		●	11,400	8.5	375				-
7.0	275	175		□	-	8.5	400	250			-
7.0	300	200		●	14,600	8.5	400	275			-
7.0	325			□	-	8.5	500	325			-
7.0	350	225		●	19,600	8.5	600	350			-
7.0	375				-	8.6	250	150			-
7.0	400	250			-	8.6	300	200			-
7.0	400	275			-	8.7	250	150			-
7.1	250				-	8.7	300	200		□	-
7.2	250	150		□	-	8.7	350	250			-
7.3	250				-	8.8	250	150			-
7.4	250				-	8.8	300	200			-
7.5	200	100			-	8.9	250	150			-
7.5	225	125			-	8.9	300	200			-
7.5	250	150			-	9.0	200	100			-
7.5	275	175		●	11,200	9.0	225	125			-
7.5	300			□	-	9.0	250	150		●	10,600
7.5	325	200		●	14,300	9.0	275	175		□	-
7.5	350	225		●	19,300	9.0	300	200		●	13,700