

NK-3100

標準フランジ式フレキシブルホース
Standard flange type

■用途 Use

配管誤差調整・変位吸収
※ねじれは吸収できません。

Adjustment of piping, Lateral deflection.
*Do not torque the hose.

■特徴 Feature

専用カラーをチューブに溶接して、フランジを取り付けています。

国土交通省の仕様にも対応。※ANSI・DIN対応可能

適用チューブ：STD

口径：15A～250A 長さ：150mm～3M

※長さについてはご相談下さい。


This product welds a collar to a tube.

Applicable tube: STD

Select the tube to match the use conditions.

Nominal DIA Length: 150mm~3M

*Please contact us about the length.



①チューブ	SUS304・SUS316L
②ブレード	SUS304
③カラー	SUS304・SUS316L
④ルーズフランジ	SS400・SUS304・SUS316L・FCD絶縁コート

①炭素鋼継手

規格：JIS・JPI・ANSI・DIN その他特殊フランジ

適用流体：水・油・空気・蒸気・薬品

※ステンレスを腐蝕させない流体に限る。

使用温度：-10～300℃ ※シール材考慮せず。

使用圧力：0.1～1.0MPa

※圧力が高い場合はご相談下さい。

②ステンレス鋼継手

規格：JIS・JPI・ANSI・DIN その他特殊フランジ

適用流体：水・油・空気・蒸気・薬品

※ステンレスを腐蝕させない流体に限る。

使用温度：-40～450℃ ※シール材考慮せず。

使用圧力：0.1～1.0MPa

※圧力が高い場合はご相談下さい。

③絶縁コート継手

規格：JIS

適用流体：給水(上水・中水)

使用温度：20～40℃

使用圧力：0.1～1.0MPa

※継手材質はご使用条件に合わせて選定をお願いします。

①Carbon steel flange.

Standard: JIS, JPI, ANSI, DIN *Available for other dimensions

Applicable fluid: Water, Oil, Air, Steam, Chemical fluid

*Limited to fluid that does not corrode stainless steel.

Operating temperature: -10~300°C *Without sealing material consideration.

Operating Pressure 0.1~1.0MPa

*Please contact us about the high pressure.

②Stainless steel flange.

Standard: JIS, JPI, ANSI, DIN *Available for other dimensions

Applicable fluid: Water, Oil, Air, Steam, Chemical fluid

*Limited to fluid that does not corrode stainless steel.

Operating temperature: -40~450°C *Without sealing material consideration.

Operating Pressure 0.1~1.0MPa

*Please contact us about the high pressure.

③Insulation coating flange.

Standard: JIS

Applicable fluid: Water supply

Operating temperature: 20~40°C

Operating Pressure 0.1~1.0MPa

*The material of the fitting wishes selection according to the license agreement.

オプション Option

ガードスプリング(GS)：曲げ半径補正
ガラスクロス(GB)：熱影響緩和
エアロフレックス®(AF)：結露防止

例)NK-3100-GS/SS400
例)NK-3100-GB/SUS304
例)NK-3100-AF/SUS304

Spring Guard: Bending radius compensation.
Insulating Jackets: Protective to high temperature.
Protective Cover: Dew condensation prevention.