

製品情報



対象被削材



技術資料 >> 1995

ISO13399記号 >> 1966

マークの見方 >> 670

エンドミル選定目安表 >> 688




図1




図2




図3

	DC ≤ 20	DC > 20
	0 + 0.030	0 + 0.040

●標準在庫 単位:mm

呼び記号	DC	APMX	LF	DCON	刃数	在庫	插图
VA4MCD0300	3	10	50	6	4	●	1
VA4MCD0400	4	12	60	8	4	●	1
VA4MCD0500	5	15	60	8	4	●	1
VA4MCD0600	6	15	60	8	4	●	1
VA4MCD0700	7	20	65	10	4	●	1
VA4MCD0800	8	20	65	10	4	●	1
VA4MCD0900	9	25	75	10	4	●	1
VA4MCD1000	10	25	75	10	4	●	2
VA4MCD1100	11	30	85	12	4	●	1
VA4MCD1200	12	30	85	12	4	●	2
VA4MCD1300	13	35	90	12	4	●	3
VA4MCD1400	14	35	95	16	4	●	1
VA4MCD1500	15	40	100	16	4	●	1
VA4MCD1600	16	40	100	16	4	●	2
VA4MCD1700	17	40	100	16	4	●	3
VA4MCD1800	18	40	100	16	4	●	3
VA4MCD1900	19	45	115	20	4	●	1
VA4MCD2000	20	45	115	20	4	●	2
VA4MCD2200	22	45	115	20	4	●	3
VA4MCD2400	24	50	120	25	4	●	1
VA4MCD2500	25	50	120	25	4	●	2
VA4MCD2800	28	55	125	25	4	●	3
VA4MCD3000	30	55	125	25	4	●	3