

回転工具用インサート

被削材	P	鋼	●	●	●	●	●	●	●	●	●	●	●	●	切削状態(目安): ●: 安定切削 ●: 一般切削 ✦: 不安定切削 ホーニング: E: 丸ホーニング F: シャープエッジ T: チャンファーホーニング								
	M	ステンレス鋼	●	●	●	●	●	●	●	●	●	●	●	●									
	K	鋳鉄	●	●	●	●	●	●	●	●	●	●	●	●									
N	非鉄金属	●	●	●	●	●	●	●	●	●	●	●	●	●									
S	耐熱合金、チタン合金	●	●	●	●	●	●	●	●	●	●	●	●	●									
H	高硬度鋼	●	●	●	●	●	●	●	●	●	●	●	●	●									
対応カッタ インサート 外観	呼び記号	精度	ホーニング	コーティング										サーメット	超硬	寸法 (mm)				形状			
				F7030	MC5020	MP6120	MP6130	MP7130	MP7140	MP9120	MP9130	VP15TF	VP20RT	VP30RT	MX3030	NX2525	NX4545	UTi20T	HTi10		TF15	IC	S
	SNC43B2G	C	F															●	12.7	4.8	2	—	
	SNC43B2S	C	T*1															●	12.7	4.8	2	—	
	SNK43B2G	K	F															●	12.7	4.8	2	—	
	SNK43B2S	K	T*1															●	12.7	4.8	2	—	
	SNGU140812ANFR-L	G	F															●	14	8.4	1.5	1.2	
	SNGU140812ANER-L	G	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNGU140812ANER-M	G	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNMU140812ANER-M	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNMU140812ANER-R	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNMU140812ANER-H	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNGU140812ANEL-M	G	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
	SNMU140812ANEL-M	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2	
SNMU140812ANEL-R	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	14	8.4	1.5	1.2		
	SNKF43B2S	K	T															●	12.7	4.8	2	—	
	SNMF43B2G	M	E	●															12.7	4.8	2	—	
	SNMN120408	M	E	●															12.7	4.78	—	0.8	
	SNMN120412	M	E	●															12.7	4.78	—	1.2	
	SOET12T308PEER-JL	E	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	12.7	3.97	1.4	0.8	
	SOGT12T308PEFR-JP	G	F															●	12.7	3.97	1.4	0.8	
	SOMT12T308PEER-JH	M	E	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	12.7	3.97	1.4	0.8	

*1 UTi20Tのホーニングは"E"です。

●: 標準在庫品(1ケース10個入りです)



回転工具用インサート