

ASX445

汎用一般切削用

製品情報




対象被削材



マークの見方 >> 1320
技術資料 >> 1989


ISO13399記号 >> 1966



- 高精度無研削形
20°ポジティブインサート
- スクリューオン式
クランプ
- 加工用途に合った
チップブレーカ
- 超硬シートの採用で高剛性

アーバタイプ

KAPR :45°
GAMP: +20° - +23° T: +4°49' - +9°53'
GAMF: -13° - -10° I: +22°55' - +23°02'



形式	呼び記号	在庫 R	刃数	寸法(mm)										WT* (kg)	APMX (mm)	図
				DC	DCX	LF	DCON	CBDP	DAH	DCCB	DCSFMS	KWW	L8			
標準形	ASX445-050A03R	●	3	50	63.0	40	22	20	11	—	45	10.4	6.3	0.5	6	1
	ASX445-063A04R	●	4	63	75.9	40	22	20	11	—	50	10.4	6.3	0.7	6	1
	ASX445R08004C	●	4	80	93.2	50	25.4	26	—	38	56	9.5	6	1.1	6	2
	ASX445R10005D	●	5	100	113.2	50	31.75	32	—	45	70	12.7	8	1.8	6	2
	ASX445R12506E	●	6	125	138.0	63	38.1	35	—	60	80	15.9	10	2.9	6	2
	ASX445R16007F	●	7	160	173.0	63	50.8	38	—	80	100	19.1	11	4.7	6	2
	ASX445R20008K	●	8	200	212.9	63	47.625	35	—	140	175	25.4	14.22	7.9	6	3
	ASX445R25010K	●	10	250	262.9	63	47.625	35	—	180	220	25.4	14.22	12.9	6	3
	ASX445R31514P	●	14	315	327.9	63	47.625	40	—	245	285	25.4	14.22	22.4	6	4
多刃形	ASX445-050A04R	●	4	50	63.0	40	22	20	11	—	45	10.4	6.3	0.4	6	1
	ASX445-063A05R	●	5	63	75.9	40	22	20	11	—	50	10.4	6.3	0.6	6	1
	ASX445R08006C	●	6	80	93.2	50	25.4	26	—	38	56	9.5	6	1.0	6	2
	ASX445R10007D	●	7	100	113.2	50	31.75	32	—	45	70	12.7	8	1.7	6	2
	ASX445R12508E	●	8	125	138.0	63	38.1	35	—	60	80	15.9	10	2.8	6	2
	ASX445R16010F	●	10	160	173.0	63	50.8	38	—	80	100	19.1	11	4.6	6	2
	ASX445R20012K	●	12	200	212.9	63	47.625	35	—	140	175	25.4	14.22	7.8	6	3
	ASX445R25014K	●	14	250	262.9	63	47.625	35	—	180	220	25.4	14.22	12.8	6	3
	ASX445R31518P	●	18	315	327.9	63	47.625	40	—	245	285	25.4	14.22	22.2	6	4
超多刃形	ASX445-050A05R	●	5	50	63.0	40	22	20	11	—	45	10.4	6.3	0.4	6	1
	ASX445-063A06R	●	6	63	75.9	40	22	20	11	—	50	10.4	6.3	0.6	6	1
	ASX445R08008C	●	8	80	93.2	50	25.4	26	—	38	56	9.5	6	1.1	6	2
	ASX445R10010D	●	10	100	113.2	50	31.75	32	—	45	70	12.7	8	1.8	6	2
	ASX445R12512E	●	12	125	138.0	63	38.1	35	—	60	80	15.9	10	2.9	6	2
	ASX445R16016F	●	16	160	173.0	63	50.8	38	—	80	100	19.1	11	4.7	6	2
	ASX445R20020K	●	20	200	212.9	63	47.625	35	—	140	175	25.4	14.22	7.8	6	3
	ASX445R25024K	●	24	250	262.9	63	47.625	35	—	180	220	25.4	14.22	12.8	6	3
	ASX445R31528P	●	28	315	327.9	63	47.625	40	—	245	285	25.4	14.22	21.8	6	4

* WT : カッタ質量

● : 標準在庫品