





G-LIST No | FL1057

高送りラジラスカッタ 柄付きタイプ

High Feed Radius Cutter with Shank Type

PDR SS/MT/CN

切削条件 Cutting Conditions P977



(単位:mm) (Unit:mm)

ツールNo. EDP No.	呼び Designation	カッタ 外径 DCX	外径 DC	刃数 ZEFP	シャンク径 DCON	全長 LF	首下長 LH	首径 DN	シャンク長 LS	重量 (kg)	形状 タイプ Type	標準価格 (Yen)
7800000	PDR20R040SS42-2S	40	20	2	42	150	50	38.9	100	1.46	1	47,100
7800001	PDR20R040MT5M16-2S	40	20	2	MT5-M16	256	120	38.9	136	2.48	2	71,100
7800003	PDR20R040MT5M24-2S	40	20	2	MT5-M24	256	120	38.9	136	2.30	2	71,100
7800009	PDR20R040SS42-2L	40	20	2	42	250	150	38.9	100	2.44	1	64,200
7800010	PDR20R040MT5M16-2L	40	20	2	MT5-M16	306	170	38.9	136	2.97	2	85,600
7800012	PDR20R040MT5M24-2L	40	20	2	MT5-M24	306	170	38.9	136	2.82	2	85,600
7800004	PDR20R050SS42-3S	50	30	3	42	150	50	48.5	100	1.55	1	64,100
7800008	PDR20R050CN50.8-3S	50	30	3	CN50.8	150	65	48.5	85	2.05	3	74,400
7800005	PDR20R050MT5M16-3S	50	30	3	MT5-M16	256	120	48.5	136	2.92	2	88,200
7800007	PDR20R050MT5M24-3S	50	30	3	MT5-M24	256	120	48.5	136	2.71	2	88,200
7800013	PDR20R050SS42-3L	50	30	3	42	250	150	48.5	100	3.03	1	78,200
7800017	PDR20R050CN50.8-3L	50	30	3	CN50.8	250	165	48.5	85	3.50	3	90,100
7800014	PDR20R050MT5M16-3L	50	30	3	MT5-M16	306	170	48.5	136	3.63	2	99,600
7800016	PDR20R050MT5M24-3L	50	30	3	MT5-M24	306	170	48.5	136	3.49	2	99,600

適用インサートと部品はp.896をご覧ください。
See p.896 for available inserts and parts.