




G-LIST No | FL1071

正面フライス スクエアタイプ ポアタイプ
45° Face Milling Square Insert Type with Bore Type


PAS BORE

切削条件 Cutting Conditions | P967



(単位:mm) (Unit:mm)

ツールNo. EDP No.	呼び Designation	外径 DC	カッタ 外径 DCX	刃数 ZEPF	カッタ 高さ LF	ボス径 DCSFMS	穴径 DCON	端面キー溝 Key Slot		APMX	重量 (kg)	形状タイプ Type	標準価格 (Yen)
								幅 KWW	深さ b				
7802000	PAS15R050M22-4	50	65	4	45	45	22	10.4	6.3	6.5	0.41	1	74,900
7802001	PAS15R063M22-5	63	78	5	45	50	22	10.4	6.3	6.5	0.59	1	88,200
7802002	PAS15R080M25.4-6	80	95	6	50	60	25.4	9.5	6	6.5	1.06	1	107,000
7802003	PAS15R100M31.7-7	100	115	7	50	70	31.75	12.7	8	6.5	1.52	2	127,000
7802004	PAS15R125M38.1-8	125	140	8	63	90	38.1	15.9	10	6.5	3.25	2	157,000



(単位:mm) (Unit:mm)

■適用インサート Inserts

呼び Designation	切れ刃数 No. of Cutting Edges	インサート寸法 Insert Size				コーティング材種 Grade of Coated Materials				標準価格 (Yen)
		IC	厚さ S	RE	さらい刃 (副切れ刃) BS	XC3025	XP3035	XP2040	XC1015	
SNKU1505AZER-GM	8	15.88	7.18	1.0	3.65	7819061	7814061	7813061		2,220
SNKU1505AZER-GR	8	15.88	7.18	1.0	3.65				7812060	2,220

■部品 Accessories

	ツールNo. EDP No.	呼び Designation	適用カッタ Applicable Body
 クランプねじ Clamping Screw	7808131	FS45513P (Torx 20IP)	PAS BORE φ50~125

	ツールNo. EDP No.	呼び Designation	適用カッタ Applicable Body	標準価格 (Yen)
 T型レンチ T-Handle Wrench	7808000	20IP-T (Torx 20IP)	PAS BORE φ50~125	2,290

レンチは別途ご購入下さい。 The wrenches are sold separately from the cutters.