

LTD

ロングテーパードリル

テーパードリル

製品情報



技術資料 >> 1982

ISO13399記号 >> 1966

対象被削材



マークの見方 >> 1607

ドリル選定目安表 >> 1619




図1



DC=6	6<DC≤10	10<DC≤18	18<DC≤30	30<DC≤40
0 -0.018	0 -0.022	0 -0.027	0 -0.033	0 -0.039

※LU（加工深さ）はLCF（溝長）-3DCを目安にご使用ください。

●：標準在庫

単位（mm）

呼び記号	DC	LCF	OAL	LF	PL	CZC	在庫	図番	呼び記号	DC	LCF	OAL	LF	PL	CZC	在庫	図番
LTDD0600A200M1	6.0	101.8	201.8	200	1.8	MT.1	●	1	LTDD1100A250M1	11.0	153.3	253.3	250	3.3	MT.1	●	1
LTDD0600A250M1	6.0	151.8	251.8	250	1.8	MT.1	●	1	LTDD1100A300M1	11.0	203.3	303.3	300	3.3	MT.1	●	1
LTDD0600A300M1	6.0	201.8	301.8	300	1.8	MT.1	●	1	LTDD1100A350M1	11.0	228.3	353.3	350	3.3	MT.1	●	1
LTDD0600A350M1	6.0	226.8	351.8	350	1.8	MT.1	●	1	LTDD1100A400M1	11.0	253.3	403.3	400	3.3	MT.1	●	1
LTDD0650A250M1	6.5	152.0	252.0	250	2.0	MT.1	●	1	LTDD1150A250M1	11.5	153.5	253.5	250	3.5	MT.1	●	1
LTDD0650A300M1	6.5	202.0	302.0	300	2.0	MT.1	●	1	LTDD1150A300M1	11.5	203.5	303.5	300	3.5	MT.1	●	1
LTDD0650A350M1	6.5	227.0	352.0	350	2.0	MT.1	●	1	LTDD1150A350M1	11.5	228.5	353.5	350	3.5	MT.1	●	1
LTDD0700A250M1	7.0	152.1	252.1	250	2.1	MT.1	●	1	LTDD1150A400M1	11.5	253.5	403.5	400	3.5	MT.1	●	1
LTDD0700A300M1	7.0	202.1	302.1	300	2.1	MT.1	●	1	LTDD1200A250M1	12.0	153.6	253.6	250	3.6	MT.1	●	1
LTDD0700A350M1	7.0	227.1	352.1	350	2.1	MT.1	●	1	LTDD1200A300M1	12.0	203.6	303.6	300	3.6	MT.1	●	1
LTDD0750A250M1	7.5	152.3	252.3	250	2.3	MT.1	●	1	LTDD1200A350M1	12.0	228.6	353.6	350	3.6	MT.1	●	1
LTDD0750A300M1	7.5	202.3	302.3	300	2.3	MT.1	●	1	LTDD1200A400M1	12.0	253.6	403.6	400	3.6	MT.1	●	1
LTDD0750A350M1	7.5	227.3	352.3	350	2.3	MT.1	●	1	LTDD1250A250M1	12.5	153.8	253.8	250	3.8	MT.1	●	1
LTDD0800A250M1	8.0	152.4	252.4	250	2.4	MT.1	●	1	LTDD1250A300M1	12.5	203.8	303.8	300	3.8	MT.1	●	1
LTDD0800A300M1	8.0	202.4	302.4	300	2.4	MT.1	●	1	LTDD1250A350M1	12.5	228.8	353.8	350	3.8	MT.1	●	1
LTDD0800A350M1	8.0	227.4	352.4	350	2.4	MT.1	●	1	LTDD1250A400M1	12.5	253.8	403.8	400	3.8	MT.1	●	1
LTDD0850A250M1	8.5	152.6	252.6	250	2.6	MT.1	●	1	LTDD1300A250M1	13.0	153.9	253.9	250	3.9	MT.1	●	1
LTDD0850A300M1	8.5	202.6	302.6	300	2.6	MT.1	●	1	LTDD1300A300M1	13.0	203.9	303.9	300	3.9	MT.1	●	1
LTDD0850A350M1	8.5	227.6	352.6	350	2.6	MT.1	●	1	LTDD1300A350M1	13.0	228.9	353.9	350	3.9	MT.1	●	1
LTDD0900A250M1	9.0	152.7	252.7	250	2.7	MT.1	●	1	LTDD1300A400M1	13.0	253.9	403.9	400	3.9	MT.1	●	1
LTDD0900A300M1	9.0	202.7	302.7	300	2.7	MT.1	●	1	LTDD1350A300M1	13.5	204.1	304.1	300	4.1	MT.1	●	1
LTDD0900A350M1	9.0	227.7	352.7	350	2.7	MT.1	●	1	LTDD1350A350M1	13.5	229.1	354.1	350	4.1	MT.1	●	1
LTDD0950A250M1	9.5	152.9	252.9	250	2.9	MT.1	●	1	LTDD1350A400M1	13.5	254.1	404.1	400	4.1	MT.1	●	1
LTDD0950A300M1	9.5	202.9	302.9	300	2.9	MT.1	●	1	LTDD1350A450M1	13.5	304.1	454.1	450	4.1	MT.1	●	1
LTDD0950A350M1	9.5	227.9	352.9	350	2.9	MT.1	●	1	LTDD1350A500M1	13.5	354.1	504.1	500	4.1	MT.1	●	1
LTDD0950A400M1	9.5	252.9	402.9	400	2.9	MT.1	●	1	LTDD1350A600M1	13.5	404.1	604.1	600	4.1	MT.1	●	1
LTDD1000A250M1	10.0	153.0	253.0	250	3.0	MT.1	●	1	LTDD1400A300M1	14.0	204.2	304.2	300	4.2	MT.1	●	1
LTDD1000A300M1	10.0	203.0	303.0	300	3.0	MT.1	●	1	LTDD1400A350M1	14.0	229.2	354.2	350	4.2	MT.1	●	1
LTDD1000A350M1	10.0	228.0	353.0	350	3.0	MT.1	●	1	LTDD1400A400M1	14.0	254.2	404.2	400	4.2	MT.1	●	1
LTDD1000A400M1	10.0	253.0	403.0	400	3.0	MT.1	●	1	LTDD1400A450M1	14.0	304.2	454.2	450	4.2	MT.1	●	1
LTDD1050A250M1	10.5	153.2	253.2	250	3.2	MT.1	●	1	LTDD1400A500M1	14.0	354.2	504.2	500	4.2	MT.1	●	1
LTDD1050A300M1	10.5	203.2	303.2	300	3.2	MT.1	●	1	LTDD1400A600M1	14.0	404.2	604.2	600	4.2	MT.1	●	1
LTDD1050A350M1	10.5	228.2	353.2	350	3.2	MT.1	●	1	LTDD1450A300M2	14.5	179.4	304.4	300	4.4	MT.2	●	1
LTDD1050A400M1	10.5	253.2	403.2	400	3.2	MT.1	●	1	LTDD1450A350M2	14.5	229.4	354.4	350	4.4	MT.2	●	1