

製品情報

対象被削材



部品規格 >> 1929

技術資料 >> 1982

ISO13399記号 >> 1966

マークの見方 >> 1607




図1

-	*Dref.		
	ø17-ø33	ø33.5-ø47	ø48-ø63
2D, 3D	+0.25 0	+0.3 0	+0.3 0
4D, 5D	+0.35 0	+0.4 0	+0.45 0
6D	+0.45 0	+0.6 0	

*Dref. : 加工公差の目安 (mm) ,

● : 標準在庫

単位 (mm)

DC (mm)	加工穴深さ (l/d)	呼び記号	在庫	刃数	LU	LBX	LPR	OAL	DCON	DCSFMS	S10	インサート呼び記号	クランプねじ	レンチ
17.0	2	MVX1700X2F20	●	2	34	41	56	99	20.0	25	0.50	SO**0630	TPS25	TIP07F
17.0	3	MVX1700X3F20	●	2	51	58	73	116	20.0	25	0.50	SO**0630	TPS25	TIP07F
17.0	4	MVX1700X4F20	●	2	68	75	90	133	20.0	25	0.50	SO**0630	TPS25	TIP07F
17.0	5	MVX1700X5F20	●	2	85	92	107	150	20.0	25	0.50	SO**0630	TPS25	TIP07F
17.0	6	MVX1700X6F20	●	2	102	109	124	167	20.0	25	0.50	SO**0630	TPS25	TIP07F
17.5	2	MVX1750X2F25	●	2	35	42	62	112	25.0	32	0.45	SO**0630	TPS25	TIP07F
17.5	3	MVX1750X3F25	●	2	52.5	59.5	79.5	129.5	25.0	32	0.45	SO**0630	TPS25	TIP07F
17.5	4	MVX1750X4F25	●	2	70	77	97	147	25.0	32	0.45	SO**0630	TPS25	TIP07F
17.5	5	MVX1750X5F25	●	2	87.5	94.5	114.5	164.5	25.0	32	0.45	SO**0630	TPS25	TIP07F
17.5	6	MVX1750X6F25	●	2	105	112	132	182	25.0	32	0.45	SO**0630	TPS25	TIP07F
18.0	2	MVX1800X2F25	●	2	36	43	63	113	25.0	32	0.40	SO**0630	TPS25	TIP07F
18.0	3	MVX1800X3F25	●	2	54	61	81	131	25.0	32	0.40	SO**0630	TPS25	TIP07F
18.0	4	MVX1800X4F25	●	2	72	79	99	149	25.0	32	0.40	SO**0630	TPS25	TIP07F
18.0	5	MVX1800X5F25	●	2	90	97	117	167	25.0	32	0.40	SO**0630	TPS25	TIP07F
18.0	6	MVX1800X6F25	●	2	108	115	135	185	25.0	32	0.40	SO**0630	TPS25	TIP07F
18.5	2	MVX1850X2F25	●	2	37	44	64	114	25.0	32	0.35	SO**0630	TPS25	TIP07F
18.5	3	MVX1850X3F25	●	2	55.5	62.5	82.5	132.5	25.0	32	0.35	SO**0630	TPS25	TIP07F
18.5	4	MVX1850X4F25	●	2	74	81	101	151	25.0	32	0.35	SO**0630	TPS25	TIP07F
18.5	5	MVX1850X5F25	●	2	92.5	99.5	119.5	169.5	25.0	32	0.35	SO**0630	TPS25	TIP07F
18.5	6	MVX1850X6F25	●	2	111	118	138	188	25.0	32	0.35	SO**0630	TPS25	TIP07F
19.0	2	MVX1900X2F25	●	2	38	45	65	115	25.0	32	0.30	SO**0630	TPS25	TIP07F
19.0	3	MVX1900X3F25	●	2	57	64	84	134	25.0	32	0.30	SO**0630	TPS25	TIP07F
19.0	4	MVX1900X4F25	●	2	76	83	103	153	25.0	32	0.30	SO**0630	TPS25	TIP07F
19.0	5	MVX1900X5F25	●	2	95	102	122	172	25.0	32	0.30	SO**0630	TPS25	TIP07F
19.0	6	MVX1900X6F25	●	2	114	121	141	191	25.0	32	0.30	SO**0630	TPS25	TIP07F
19.5	2	MVX1950X2F25	●	2	39	46	66	116	25.0	32	0.25	SO**0630	TPS25	TIP07F
19.5	3	MVX1950X3F25	●	2	58.5	65.5	85.5	135.5	25.0	32	0.25	SO**0630	TPS25	TIP07F
19.5	4	MVX1950X4F25	●	2	78	85	105	155	25.0	32	0.25	SO**0630	TPS25	TIP07F
19.5	5	MVX1950X5F25	●	2	97.5	104.5	124.5	174.5	25.0	32	0.25	SO**0630	TPS25	TIP07F