


外觀図

SPPC-SP ストレート ネジ部材質：特殊ステンレスまたはSUS303




単位：mm

形式	チューブ外径 ϕD	R	A	B	L	チューブエンド C	対辺 H	質量 (g)	オリフィス径 (ϕ mm)	価格 (\yen)
SPPC4-M3SP	4	M3×0.5	2.5	20.1	17.6	14.9	10	5.5	1.2	720
SPPC4-M5SP		M5×0.8	3	20	17				1.8	610
SPPC4-01SP		R1/8	8	21	15			3	7.5	590
SPPC4-02SP		R1/4	11							
SPPC6-M5SP	6	M5×0.8	3	22.1	19.1	17	12	8.3	1.8	730
SPPC6-01SP		R1/8	8	22.6	18.6			8.4	670	
SPPC6-02SP		R1/4	11	24.6	18.5		14	16	4.6	730
SPPC6-03SP		R3/8	12	23.6	17.2		17	25	750	
SPPC8-01SP	8	R1/8	8	27.9	23.9	18.2	14	14	6	780
SPPC8-02SP		R1/4	11	26.6	20.6				7	810
SPPC8-03SP		R3/8	12	23.9	17.6		17	21	830	
SPPC10-02SP	10	R1/4	11	29.8	23.8	20.7	17	18	8.5	980
SPPC10-03SP		R3/8	12	29.3	23			24		990
SPPC12-03SP	12	R3/8	12	31.9	25.6	23.3	21	32	11	1,180
SPPC12-04SP		R1/2	15	33.9	25.7			46		1,170

※テーパネジタイプのL寸法は、ねじ締付け後の参考寸法です。

SPPL-SP エルボ ネジ部材質：特殊ステンレスまたはSUS303



単位：mm

形式	チューブ外径 ϕD	R	A	B	L	ϕP	チューブエンド C	E	対辺 H	質量 (g)	オリフィス径 (ϕ mm)	価格 (\yen)
SPPL4-M3SP	4	M3×0.5	2.5	19.8	22.3	10	14.9	18	10	6	1.2	750
SPPL4-M5SP		M5×0.8	3	20.3						6.9	1.8	680
SPPL4-01SP		R1/8	8	23.3	24.3				2.8	9.5	650	
SPPL4-02SP		R1/4	11	26.3	25.3							14
SPPL6-M5SP	6	M5×0.8	3	22	25.3	12.5	16.8	19.8	12	11	1.8	770
SPPL6-01SP		R1/8	8	25	27.3				13	740		
SPPL6-02SP		R1/4	11	28	28.2				14	19	4.6	800
SPPL6-03SP		R3/8	12	29.8	29.7				17	31	820	
SPPL8-01SP	8	R1/8	8	28	31.3	14.5	18.1	22.7	14	16	6	800
SPPL8-02SP		R1/4	11	31	32.2				21	800		
SPPL8-03SP		R3/8	12	32.8	33.7				17	33	820	
SPPL10-02SP	10	R1/4	11	36	38.7	17.5	20.2	26.2	17	30	8	920
SPPL10-03SP		R3/8	12	37	39.4				37	910		
SPPL12-03SP	12	R3/8	12	39	43.2	21	23.4	29.4	21	46	10	1,230
SPPL12-04SP		R1/2	15	42	44.3					60		1,320

※テーパネジタイプのL寸法は、ねじ締付け後の参考寸法です。