


PAT トリプルブランチエイ

RoHS対応

OP.
P.868

CAD
2D & 3D



単位：mm

形 式	チューブ外径 D	R	A	B	L1	L2	J1	J2	P1	P2	フィッティング C	E	対辺 H	オリフィス (mm)	質量 (g)	CAD ファイル名
PAT4-01④	4	R1/8	8	54.7	50.7	15.5	13	10	10	15.4	14.9	22.2	14	3	40	PAT4-01
PAT4-02④		R1/4	11	57.7	51.7	16.5							46		PAT4-02	
PAT4-03④		R3/8	12	59.7	53.4	18.2							17		60	PAT4-03
PAT6-01④	6	R1/8	8	54.7	50.7	15.5	13	12	12.5	15.4	17	24.2	14	3.7	45	PAT6-01
PAT6-02④		R1/4	11	57.7	51.7	16.5							51		PAT6-02	
PAT6-03④		R3/8	12	59.7	53.4	18.2							17		65	PAT6-03
PAT8-01④	8	R1/8	8	61.7	57.7	17.5	15	14	14.5	19	18.1	27.7	17	6	71	PAT8-01
PAT8-02④		R1/4	11	64.7	58.7	18.5							73		PAT8-02	
PAT8-03④		R3/8	12	65.7	59.4	19.2							81		PAT8-03	
PAT8-04④		R1/2	15	70.7	62.5	22.3							22		113	PAT8-04
PAT10-02④	10	R1/4	11	75.7	69.7	22	18	17	17.5	23	20.2	31.7	22	7.5	122	PAT10-02
PAT10-03④		R3/8	12	76.7	70.4	22.7									126	PAT10-03
PAT10-04④		R1/2	15	79.7	71.5	23.8									142	PAT10-04
PAT12-02④	12	R1/4	11	89.5	83.5	26.8	21.6	20	21	27	23.4	36.7	27	8.5	203	PAT12-02
PAT12-03④		R3/8	12	90.5	84.2	27.5								9.7	205	PAT12-03
PAT12-04④		R1/2	15	93.5	85.3	28.6								214	PAT12-04	
PAT1/4-01④	1/4	R1/8	8	54.7	50.7	15.5	13	12	12.5	15.4	17	24.2	14	4.1	45	PAT1_4-01
PAT1/4-02④		R1/4	11	57.7	51.7	16.5							50		PAT1_4-02	
PAT1/4-03④		R3/8	12	59.7	53.4	18.2							17		64	PAT1_4-03
PAT5/16-02④	5/16	R1/4	11	64.7	58.7	18.5	15	14	14.5	19	18.1	27.7	17	6	73	PAT5_16-02
PAT5/16-03④		R3/8	12	65.7	59.4	19.2							81		PAT5_16-03	
PAT5/16-04④		R1/2	15	70.7	62.5	22.3							22		113	PAT5_16-04
PAT3/8-02④	3/8	R1/4	11	75.7	69.7	22	18	17	17.5	23	20.2	31.7	22	7.5	124	PAT3_8-02
PAT3/8-03④		R3/8	12	76.7	70.4	22.7									125	PAT3_8-03
PAT3/8-04④		R1/2	15	79.7	71.5	23.8									143	PAT3_8-04

※1.形式内の④には、外観色：ブラック以外で、通常包装以外を希望の場合、選択して記入してください。

外観色：ライトグレー⇒記号：W、包装仕様：クリーンルーム包装⇒記号：-C、

外観色：ライトグレー & 包装仕様：クリーンルーム包装⇒記号：W-C、クリーン洗浄 & 包装仕様：クリーンルーム包装⇒記号：-UC

※2. L1、L2寸法は、ねじ締付け後の参考寸法です。

※3. オリフィス径は、最小流路を直径換算しています。