

製品情報

対象被削材



部品規格 >> 1929

技術資料 >> 1982

ISO13399記号 >> 1966

マークの見方 >> 1607




図1

※フランジ部のねじ穴はクーラント穴ではありません。

●：標準在庫 単位 (mm)

DC (mm)	加工穴深さ (l/d)	呼び記号	在庫	刃数	LU	LBX	LPR	OAL	DCON	DCSFMS	CNT	インサート呼び記号	クランプねじ	レンチ
12.0	2	TAFS1200F20	●	2	24	29	39	82.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
12.0	3	TAFM1200F20	●	2	36	41	51	94.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
12.5	2	TAFS1250F20	●	2	25	29	39	82.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
12.5	3	TAFM1250F20	●	2	37.5	41	51	94.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
13.0	2	TAFS1300F20	●	2	26	31	41	84.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
13.0	3	TAFM1300F20	●	2	39	44	54	97.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
13.5	2	TAFS1350F20	●	2	27	31	41	84.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
13.5	3	TAFM1350F20	●	2	40.5	44	54	97.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
14.0	2	TAFS1400F20	●	2	28	33	43	86.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
14.0	3	TAFM1400F20	●	2	42	47	57	100.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
14.5	2	TAFS1450F20	●	2	29	33	43	86.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
14.5	3	TAFM1450F20	●	2	43.5	47	57	100.0	20.0	25	PT1/8	GC**0402	TS2	TKY06F
15.0	2	TAFS1500F20	●	2	30	35	45	88.0	20.0	25	PT1/8	GP**0602	TS2	TKY06F
15.0	3	TAFM1500F20	●	2	45	50	60	103.0	20.0	25	PT1/8	GP**0602	TS2	TKY06F
15.5	2	TAFS1550F20	●	2	31	35	45	88.0	20.0	25	PT1/8	GP**0602	TS2	TKY06F
15.5	3	TAFM1550F20	●	2	46.5	50	60	103.0	20.0	25	PT1/8	GP**0602	TS2	TKY06F
16.0	2	TAFS1600F25	●	2	32	38	57	107.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
16.0	3	TAFM1600F25	●	2	48	54	73	123.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
16.0	4	TAFM1600F25	●	2	64	70	89	139.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
16.5	2	TAFS1650F25	●	2	33	38	57	107.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
16.5	3	TAFM1650F25	●	2	49.5	54	73	123.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
17.0	2	TAFS1700F25	●	2	34	41	59	109.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
17.0	3	TAFM1700F25	●	2	51	58	76	126.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
17.0	4	TAFM1700F25	●	2	68	75	93	143.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
17.5	2	TAFS1750F25	●	2	35	41	59	109.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
17.5	3	TAFM1750F25	●	2	52.5	58	76	126.0	25.0	35	PT1/8	GP**0602	TS2	TKY06F
18.0	2	TAFS1800F25	●	2	36	43	61	111.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F
18.0	3	TAFM1800F25	●	2	54	61	79	129.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F
18.0	4	TAFM1800F25	●	2	72	79	97	147.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F
18.5	2	TAFS1850F25	●	2	37	43	61	111.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F
18.5	3	TAFM1850F25	●	2	55.5	61	79	129.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F
19.0	2	TAFS1900F25	●	2	38	46	63	113.0	25.0	35	PT1/8	GP**0702	TS25	TKY08F