




詳細 P.63

RoHS10	シャック径 D 公差	材質 硬度	型式		刃先形状は下記(A)(D)(R)(E)(G)より選択
			Type	刃先形状 刃先長さ	
Dm5 (D3~25)		SKD11相当 60~63HRC 表面3000HV	T-SP	(A)	
		粉末ハイス鋼 62~64HRC 表面3000HV	T-PH	(D)	
D ^{+0.005} ₀ (D3~13)		SKD11相当 60~63HRC 表面3000HV	AT-SP	(R)	
		粉末ハイス鋼 62~64HRC 表面3000HV	AT-PH	(E) (G)	

シャック径公差Dはm5, +0.005/0 選択

刃先長さ(B)
X>L>S



型式	Type	刃先形状	刃先長さ	指定0.01mm単位										B	H				
				L												R(D)			
				(A)		D		R		E		G							
				3	4	5	6	7	8			min. P	max.	P·Kmax.	P·Wmin.				
(Dm5)	T-SP	S		3	40	50	60	70	80			1.00	2.99	-	-				
				4	40	50	60	70	80			1.00	3.99	3.97	1.00				
				5	40	50	60	70	80			2.00	4.99	4.97	1.20				
				6	40	50	60	70	80			2.00	5.99	5.97	1.50				
				8	(40)	50	60	70	80	90	100	3.00	7.99	7.97	2.00				
	T-PH	L			10	(40)	50	60	70	80	90	100	3.00	9.99	9.97	2.50			
					13	(40)	50	60	70	80	90	100	6.00	12.99	12.97	3.00			
					16	(40)	50	60	70	80	90	100	10.00	15.99	15.97	4.00			
					20	(40)	50	60	70	80	90	100	13.00	19.99	19.97	5.00			
					25	(40)	50	60	70	80	90	100	18.00	24.99	24.97	6.00			
(D ^{+0.005} ₀) (D3~13)	AT-SP	L		3		50	60	70	80			1.00	2.99	-	-				
				4		50	60	70	80			1.00	3.99	3.97	2.00				
				5		50	60	70	80			2.00	4.99	4.97	2.00				
				6		50	60	70	80			2.00	5.99	5.97	2.00				
				8		50	60	70	80	90	100	3.00	7.99	7.97	2.50				
	AT-PH	X			10		50	60	70	80	90	100	3.00	9.99	9.97	2.50			
					13		50	60	70	80	90	100	6.00	12.99	12.97	3.00			
					16		60	70	80	90	100	10.00	15.99	15.97	4.00				
					20		60	70	80	90	100	13.00	19.99	19.97	5.00				
					25		60	70	80	90	100	18.00	24.99	24.97	6.00				
				3		50	60	70	80			2.00	2.99						
				4		50	60	70	80			2.00	3.99						
				5		60	70	80			2.00	4.99							
				6		60	70	80			2.00	5.99							
				8		60	70	80	90	100	3.00	7.99							
					10		60	70	80	90	100	3.00	9.99						
					13		60	70	80	90	100	6.00	12.99						
					16		70	80	90	100	10.00	15.99							
					20		70	80	90	100	13.00	19.99							
					25		70	80	90	100	18.00	24.99							

Ⓜ(A) : P>D-0.03...l=0 刃先形状(A)でP>D-0.03の場合、D^{-0.01}_{-0.03}(溝入り)はつきません。
 Ⓜ(D)(R)(E)(G) : P·K>D-0.05...l=0 刃先形状(D)(R)(E)(G)でP·K>D-0.05の場合、D^{-0.01}_{-0.03}(溝入り)はつきません。
 Ⓜ(L)(40) : B=8 全長が(40)の場合、刃先長さは一律8mmになります。

Order 注文例: 型式 - L - P - W - R(D)

T-SP-EL 16 - 70 - P12.00 - W6.00

Delivery 出荷日: 3 日目出荷

ストック A

⊗追加工PRC・リテーナセット納入はストックA早割適用不可