



VY 真空破壊機能付 サイレンサ大気開放仕様

RoHS対応



回路図




単位: mm


形式	チューブ外径 øD	B	F	C1	C2	ノズル径	定格圧力 (MPa)	到達真空度 (-kPa)	吸込流量 (ℓ/min[ANR])	消費流量 (ℓ/min[ANR])	質量 (g)
VYH05-444	4	45.1	10.4	10.9	11	0.5	0.5	90	7	11.5	19
VYH05-666	6	48	10.8	11.7	11.6	0.5		92	12.5	23	20
VYH07-444	4	45.1	10.4	10.9	11	0.7	0.5	92	12.5	23	20
VYH07-666	6	48	10.8	11.7	11.6	0.7		92	12.5	23	20
VYL05-444	4	45.1	10.4	10.9	11	0.5	0.5	66	12	11.5	19
VYL05-666	6	48	10.8	11.7	11.6	0.5			18	23	19
VYL07-444	4	45.1	10.4	10.9	11	0.7	0.5	66	21	23	20
VYL07-666	6	48	10.8	11.7	11.6	0.7			21	23	20
VYE05-444	4	45.1	10.4	10.9	11	0.5	0.35	90	3	8	19
VYE05-666	6	48	10.8	11.7	11.6	0.5			3	8	20
VYE07-444	4	45.1	10.4	10.9	11	0.7	0.35	90	9	17	20
VYE07-666	6	48	10.8	11.7	11.6	0.7			9	17	20

VY 真空破壊機能付 サイレンサ大気開放仕様 真空フィルタ付

RoHS対応



回路図



単位: mm

形式	チューブ外径 øD	B	F	C1	C2	ノズル径	定格圧力 (MPa)	到達真空度 (-kPa)	吸込流量 (ℓ/min[ANR])	消費流量 (ℓ/min[ANR])	質量 (g)
VYH05-444F	4	59.7	34.1	10.9	11	0.5	0.5	90	7	11.5	21
VYH05-666F	6	62.9	34.4	11.7	11.6	0.5		92	12.5	23	22
VYH07-444F	4	59.7	34.1	10.9	11	0.7	0.5	92	12.5	23	21
VYH07-666F	6	62.9	34.4	11.7	11.6	0.7		92	12.5	23	22
VYL05-444F	4	59.7	34.1	10.9	11	0.5	0.5	66	12	11.5	21
VYL05-666F	6	62.9	34.4	11.7	11.6	0.5			18	23	22
VYL07-444F	4	59.7	34.1	10.9	11	0.7	0.5	66	21	23	21
VYL07-666F	6	62.9	34.4	11.7	11.6	0.7			21	23	22
VYE05-444F	4	59.7	34.1	10.9	11	0.5	0.35	90	3	8	21
VYE05-666F	6	62.9	34.4	11.7	11.6	0.5			3	8	22
VYE07-444F	4	59.7	34.1	10.9	11	0.7	0.35	90	9	17	21
VYE07-666F	6	62.9	34.4	11.7	11.6	0.7			9	17	22