


ミスミ

AS COATED HIGH SPEED STEEL SQUARE END MILLS

ASコートハイス鋼スクエアエンドミル

●2枚刃 / レギュラー -2 FLUTES / REGULAR-

AS-EM2R



材質 **HSS Co8%** **AS** 仕様 **レギュラー** **30°** **再研磨**

Ⓢ被削材別の適性については、AS-EM2Sをご参照ください。

型番 **AS-EM2R** 1本単位

刃径 D	刃長 l	全長 L	首下角 θ	シャンク径 d	¥通常単価 100本以上お見積り			
					1~9本	10~29本	30~49本	50~99本
1	3.5	45	15°	6	2,170	2,106	2,056	1,955
1.5	5	45	15°	6	2,040	1,978	1,939	1,838
2	7	50	15°	6	2,040	1,978	1,939	1,838
2.5	8	50	15°	6	2,040	1,978	1,939	1,838
3	10	50	15°	6	1,960	1,898	1,859	1,759
3.5	12	60	15°	8	1,770	1,719	1,682	1,593
4	12	60	15°	8	1,770	1,719	1,682	1,593
4.5	15	60	15°	8	1,770	1,719	1,682	1,593
5	15	60	15°	8	1,770	1,719	1,682	1,593
5.5	15	60	15°	8	1,770	1,719	1,682	1,593
6	15	60	15°	8	1,770	1,719	1,682	1,593
6.5	20	60	15°	10	1,960	1,898	1,859	1,759
7	20	60	15°	10	1,960	1,898	1,859	1,759
7.5	20	60	15°	10	1,960	1,898	1,859	1,759
8	20	60	15°	10	1,960	1,898	1,859	1,759
8.5	25	70	15°	10	2,280	2,218	2,167	2,053
9	25	70	15°	10	2,280	2,218	2,167	2,053
9.5	25	70	15°	10	2,280	2,218	2,167	2,053
10	25	70	—	10	2,280	2,218	2,167	2,053
11	30	80	15°	12	2,770	2,681	2,630	2,492

刃径 D	刃長 l	全長 L	首下角 θ	シャンク径 d	¥通常単価 100本以上お見積り			
					1~9本	10~29本	30~49本	50~99本
12	30	80	—	12	2,770	2,681	2,630	2,492
13	35	85	—	12	4,020	3,894	3,818	3,616
14	35	90	15°	16	4,020	3,894	3,818	3,616
15	40	95	15°	16	4,430	4,304	4,215	3,987
16	40	95	—	16	4,450	4,310	4,223	4,007
18	40	95	—	16	4,770	4,726	4,627	4,386
19	45	110	15°	20	6,850	6,648	6,509	6,167
20	45	110	—	20	5,840	5,785	5,664	5,367
22	56	122	—	20	6,460	6,394	6,262	5,933
25	60	130	—	25	7,570	7,493	7,339	6,955

切削条件 **P.435**

Order 注文例

**AS-EM2R 10**  
型番 刃径 (D)


Delivery 出荷日

**在庫品** **巻末-7**

Ⓢご希望によりPM 6:00迄、当日出荷受付致します。

●2枚刃 / ロング -2 FLUTES / LONG-

AS-EM2L



材質 **HSS Co8%** **AS** 仕様 **ロング** **30°** **再研磨**

Ⓢ被削材別の適性については、AS-EM2Sをご参照ください。

型番 **AS-EM2L** 1本単位

刃径 D	刃長 l	全長 L	首下角 θ	シャンク径 d	¥通常単価 100本以上お見積り			
					1~9本	10~29本	30~49本	50~99本
3	15	60	15°	6	2,040	1,978	1,939	1,838
4	20	60	15°	8	1,990	1,926	1,889	1,788
5	25	60	15°	8	1,990	1,926	1,889	1,788
6	25	60	15°	8	1,990	1,926	1,889	1,788
7	35	75	15°	10	2,130	2,067	2,029	1,916
8	35	75	15°	10	2,130	2,067	2,029	1,916
9	45	90	15°	10	2,590	2,514	2,464	2,337
10	45	90	—	10	2,590	2,514	2,464	2,337
11	55	105	15°	12	2,590	2,514	2,464	2,337
12	55	105	—	12	2,980	2,892	2,828	2,677
13	55	105	—	12	4,560	4,421	4,332	4,105
14	55	110	15°	16	4,560	4,421	4,332	4,105
15	65	120	15°	16	4,930	4,779	4,689	4,437
16	65	120	—	16	4,930	4,779	4,689	4,437
18	65	120	—	16	6,550	6,348	6,221	5,893
19	75	140	15°	20	6,890	6,674	6,536	6,194
20	75	140	—	20	6,240	6,185	6,053	5,735
21	75	140	—	20	7,900	7,659	7,496	7,104
22	75	140	—	20	7,600	7,361	7,209	6,829

刃径 D	刃長 l	全長 L	首下角 θ	シャンク径 d	¥通常単価 100本以上お見積り			
					1~9本	10~29本	30~49本	50~99本
23	90	160	15°	25	8,120	8,032	7,867	7,450
25	90	160	—	25	7,820	7,732	7,567	7,171
26	90	160	—	25	9,250	9,151	8,964	8,492
28	90	160	—	25	11,060	10,951	10,719	10,159
30	90	160	—	25	13,270	13,139	12,863	12,182
32	95	180	—	32	16,280	16,104	15,774	14,948
35	100	185	—	32	20,190	19,970	19,564	18,530
38	105	190	—	32	23,850	23,597	23,113	21,892
40	110	195	—	32	28,050	27,753	27,180	25,750

切削条件 **P.435**

Order 注文例

**AS-EM2L 10**  
型番 刃径 (D)

Delivery 出荷日

**在庫品** **巻末-7**

Ⓢご希望によりPM 6:00迄、当日出荷受付致します。

