


ミスミ

HSS MACHINE REAMER

ハイス鋼マシンリーマ (国内メーカー標準品)

● 右刃ストレート刃 0.1mm単位指定タイプ

MRST



刃径D	公差	刃径D	MT No.
3	+0.007 +0.002	3~14	1
3.1~6	+0.009 +0.004	14.1~23	2
6.1~10	+0.012 +0.006	23.1~30	3
10.1~18	+0.015 +0.007		
18.1~30	+0.017 +0.008		

材質



型番 MRST

1本単位

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常 単価 1~4本
3	0.5	35	110	6	7,660
3.1	0.5	35	110	6	8,420
3.2	0.5	35	110	6	8,420
3.3	0.5	35	110	6	—
3.4	0.5	35	110	6	—
3.5	0.5	35	110	6	7,660
3.6	0.5	35	110	6	—
3.7	0.5	35	110	6	—
3.8	0.5	35	110	6	8,200
3.9	0.5	35	110	6	8,200
4	0.5	35	110	6	6,910
4.1	0.5	45	120	6	7,660
4.2	0.5	45	120	6	7,660
4.3	0.5	45	120	6	—
4.4	0.5	45	120	6	—
4.5	0.5	45	120	6	6,310
4.6	1	45	120	6	—
4.7	1	45	120	6	—
4.8	1	45	120	6	—
4.9	1	45	120	6	7,660
5	1	45	120	6	6,310
5.1	1	45	120	6	7,010
5.2	1	45	120	6	7,010
5.3	1	45	120	6	7,010
5.4	1	45	120	6	—
5.5	1	45	120	6	6,310
5.6	1	50	130	6	—
5.7	1	50	130	6	6,800
5.8	1	50	130	6	6,800
5.9	1	50	130	6	6,800
6	1	50	130	6	6,130
6.1	1	50	130	6	7,010
6.2	1	50	130	6	7,010
6.3	1	50	130	6	7,010
6.4	1	50	130	6	7,010
6.5	1	50	130	6	6,310
6.6	1	55	140	6	7,010
6.7	1	55	140	6	—
6.8	1	55	140	6	—
6.9	1	55	140	6	—
7	1	55	140	6	6,310
7.1	1	55	140	6	—
7.2	1	55	140	6	7,350
7.3	1	55	140	6	—
7.4	1	55	140	6	—
7.5	1	55	140	6	6,680
7.6	1	60	150	6	—
7.7	1	60	150	6	7,350
7.8	1	60	150	6	—
7.9	1	60	150	6	7,350
8	1	60	150	6	6,680
8.1	1	60	150	6	7,660
8.2	1	60	150	6	7,660
8.3	1	60	150	6	7,660
8.4	1	60	150	6	—
8.5	1	60	150	6	6,910
8.6	1	70	160	6	7,660
8.7	1	70	160	6	7,660
8.8	1	70	160	6	7,660
8.9	1	70	160	6	7,660
9	1	70	160	6	6,910
9.1	1	70	160	6	—
9.2	1	70	160	6	7,660
9.3	1	70	160	6	7,660
9.4	1	70	160	6	—
9.5	1	70	160	6	6,910
9.6	1	70	160	6	7,660
9.7	1	70	160	6	—

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常 単価 1~4本
9.8	1	70	160	6	7,660
9.9	1	70	160	6	7,660
10	1	70	160	6	6,910
10.1	1	70	160	6	8,200
10.2	1	70	160	6	8,200
10.3	1	70	160	6	8,200
10.4	1	70	160	6	8,200
10.5	1	70	160	6	7,460
10.6	1	75	170	6	8,200
10.7	1	75	170	6	—
10.8	1	75	170	6	—
10.9	1	75	170	6	—
11	1	75	170	6	—
11.1	1	75	170	6	—
11.2	1	75	170	6	—
11.3	1	75	170	6	—
11.4	1	75	170	6	8,200
11.5	1	75	170	6	7,460
11.6	1	75	170	6	8,200
11.7	1	75	170	6	—
11.8	1	75	170	6	—
11.9	1	75	170	6	8,200
12	1	75	170	6	7,460
12.1	1	80	180	6	8,420
12.2	1	80	180	6	8,420
12.3	1	80	180	6	8,420
12.4	1	80	180	6	8,420
12.5	1	80	180	6	7,660
12.6	1	80	180	8	—
12.7	1	80	180	8	8,420
12.8	1	80	180	8	8,420
12.9	1	80	180	8	8,420
13	1	80	180	8	7,660
13.1	1	85	190	8	—
13.2	1	85	190	8	8,420
13.3	1	85	190	8	8,420
13.4	1	85	190	8	—
13.5	1	85	190	8	7,660
13.6	1	85	190	8	—
13.7	1	85	190	8	—
13.8	1	85	190	8	—
13.9	1	85	190	8	8,420
14	1	85	190	8	6,930
14.1	1.5	90	210	8	9,070
14.2	1.5	90	210	8	—
14.3	1.5	90	210	8	9,070
14.4	1.5	90	210	8	9,070
14.5	1.5	90	210	8	—
14.6	1.5	90	210	8	—
14.7	1.5	90	210	8	9,070
14.8	1.5	90	210	8	9,070
14.9	1.5	90	210	8	—
15	1.5	90	210	8	7,620
15.1	1.5	95	215	8	9,510
15.2	1.5	95	215	8	9,510
15.3	1.5	95	215	8	9,510
15.4	1.5	95	215	8	9,510
15.5	1.5	95	215	8	8,630
15.6	1.5	95	215	8	—
15.7	1.5	95	215	8	—
15.8	1.5	95	215	8	9,510
15.9	1.5	95	215	8	9,510
16	1.5	95	215	8	8,630
16.1	1.5	100	220	8	11,320
16.2	1.5	100	220	8	11,320
16.3	1.5	100	220	8	11,320
16.4	1.5	100	220	8	—
16.5	1.5	100	220	8	10,250

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常 単価 1~4本
16.6	1.5	100	220	8	11,320
16.7	1.5	100	220	8	11,320
16.8	1.5	100	220	8	—
16.9	1.5	100	220	8	—
17	1.5	100	220	8	10,250
17.1	1.5	105	225	8	12,070
17.2	1.5	105	225	8	12,070
17.3	1.5	105	225	8	—
17.4	1.5	105	225	8	12,070
17.5	1.5	105	225	8	—
17.6	1.5	105	225	8	—
17.7	1.5	105	225	8	13,500
17.8	1.5	105	225	8	—
17.9	1.5	105	225	8	13,500
18	1.5	105	225	8	9,100
18.1	1.5	105	225	8	13,500
18.2	1.5	105	225	8	13,500
18.3	1.5	105	225	8	—
18.4	1.5	105	225	8	—
18.5	1.5	105	225	8	12,200
18.6	1.5	105	225	8	13,500
18.7	1.5	105	225	8	13,500
18.8	1.5	105	225	8	13,500
18.9	1.5	105	225	8	13,500
19	1.5	105	225	8	11,110
19.1	1.5	110	230	8	13,580
19.2	1.5	110	230	8	13,580
19.3	1.5	110	230	8	—
19.4	1.5	110	230	8	13,580
19.5	1.5	110	230	8	—
19.6	1.5	110	230	8	—
19.7	1.5	110	230	8	—
19.8	1.5	110	230	8	—
19.9	1.5	110	230	8	13,580
20	1.5	110	230	8	12,400
20.1	1.5	120	240	8	14,910
20.2	1.5	120	240	8	14,910
20.3	1.5	120	240	8	14,910
20.4	1.5	120	240	8	—
20.5	1.5	120	240	8	13,500
20.6	1.5	120	240	8	14,910
20.7	1.5	120	240	8	—
20.8	1.5	120	240	8	14,910
20.9	1.5	120	240	8	—
21	1.5	120	240	8	13,160
21.1	1.5	120	240	8	—
21.2	1.5	120	240	8	—
21.3	1.5	120	240	8	—
21.4	1.5	120	240	8	—
21.5	1.5	120	240	8	—
21.6	1.5	120	240	8	—
21.7	1.5	120	240	8	—
21.8	1.5	120	240	8	—
21.9	1.5	120	240	8	15,210
22	1.5	120	240	8	11,460
22.1	1.5	130	250	8	17,460
22.2	1.5	130	250	8	17,460
22.3	1.5	130	250	8	—
22.4	1.5	130	250	8	—
22.5	1.5	130	250	8	15,850
22.6	1.5	130	250	8	—
22.7	1.5	130	250	8	—
22.8	1.5	130	250	8	17,460
22.9	1.5	130	250	8	—
23	1.5	130	250	8	14,460
23.1	1.5	130	270	8	19,520
23.2	1.5	130	270	8	—
23.3	1.5	130	270	8	—

刃径D	公差	刃径D	MT No.
3	+0.007 +0.002	3~14	1
3.1~6	+0.009 +0.004	14.1~23	2
6.1~10	+0.012 +0.006	23.1~30	3
10.1~18	+0.015 +0.007		
18.1~30	+0.017 +0.008		

刃径D	食付長 T	刃長 ℓ	全長 L	刃数	¥通常 単価 1~4本
23.4	1.5	130	270	8	—
23.5	1.5	130	270	8	—
23.6	1.5	130	270	8	—
23.7	1.5	130	270	8	19,520
23.8	1.5	130	270	8	—
23.9	1.5	130	270	8	—
24	1.5	130	270	8	17,700
24.1	1.5	130	270	8	—
24.2	1.5	130	270	8	—
24.3	1.5	130	270	8	20,380
24.4	1.5	130	270	8	—
24.5	1.5	130	270	8	18,560
24.6	1.5	130	270	8	—
24.7	1.5	130	270	8	—
24.8	1.5	130	270	8	—
24.9	1.5	130	270	8	20,380
25	1.5	130	270	8	17,560
25.1	1.5	140	280	10	—