


鋼 六角穴付きボルト(キャップスクリュー) (細目・P-1.5)(左ねじ)



A0000024

鉄



		M16
頭部径 (d k)	基準寸法	24
頭部高さ (K)	基準寸法	16
レンチサイズ (S)		14
レンチ深さ (t)	最小	8

16.0		
長さ	入り数	生産
55	1×200	●

六角穴付きボルト(UNC)(キャップスクリュー)




A0000030

鉄

A0020030

ステンレス



サイズ	UNC #1-64	UNC #2-56	UNC #3-48	UNC #4-40	UNC #5-40	UNC #6-32	UNC #8-32	UNC #10-24	UNC #12-24	UNC 1/4-20	UNC 5/16-18	UNC 3/8-16	UNC 7/16-14	UNC 1/2-13	UNC 9/16-12	UNC 5/8-11	UNC 3/4-10	
呼び径	約	1.8	2.1	2.5	2.8	3.1	3.5	4.1	4.8	5.4	6.3	7.9	9.5	11.0	12.7	14.2	15.8	19.0
ds	最大	1.854	2.184	2.514	2.844	3.175	3.505	4.165	4.826	5.486	6.35	7.937	9.525	11.112	12.7	14.287	15.875	19.050
	最小	1.765	2.087	2.410	2.730	3.053	3.375	4.025	4.673	5.334	6.184	7.754	9.342	10.906	12.494	14.066	15.654	18.811
dk	最大	2.997	3.556	4.089	4.648	5.207	5.740	6.858	7.924	8.229	9.525	11.912	14.274	16.662	19.05	21.412	23.825	28.575
	最小	2.844	3.403	3.911	4.470	5.029	5.537	6.654	7.696	7.975	9.271	11.607	13.97	16.306	18.669	21.005	23.393	28.117
k	最大	1.854	2.184	2.514	2.844	3.175	3.505	4.165	4.826	5.486	6.35	7.924	9.525	11.125	12.7	14.274	15.875	19.050
	最小	1.778	2.108	2.413	2.743	3.073	3.403	4.038	4.699	5.334	6.197	7.772	9.347	10.922	12.496	14.071	15.646	18.796
t	最小	0.787	0.965	1.117	1.295	1.447	1.625	1.955	2.286	2.616	3.048	3.835	4.622	5.410	6.223	6.604	7.797	9.398
六角穴サイズ	六角レンチ	1/16	5/64	5/64	3/32	3/32	7/64	9/64	5/32	5/32	3/16	1/4	5/16	3/8	3/8	7/16	1/2	5/8

#1			
長さ	入り数	鉄	ステンレス
1/8	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
1/2	100×1	●	●
5/8	100×1	●	●

#2			
長さ	入り数	鉄	ステンレス
3/32	100×1	●	●
1/8	100×1	●	●
5/32	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
9/16	100×1	●	●
5/8	100×1	●	●
3/4	100×1	●	●
7/8	100×1	●	●
1"	100×1	●	●
1"1/4	100×1	●	●
1"1/2	100×1	●	●

#3			
長さ	入り数	鉄	ステンレス
1/8	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
5/8	100×1	●	●
3/4	100×1	●	●
7/8	100×1	●	●
1"	100×1	●	●
1"1/4	100×1	●	●

#4			
長さ	入り数	鉄	ステンレス
1/8	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
9/16	100×1	●	●
5/8	100×1	●	●
3/4	100×1	●	●
7/8	100×1	●	●
1"	100×1	●	●
1"1/8	100×1	●	●
1"1/4	100×1	●	●
1"3/8	100×1	●	●
1"1/2	100×1	●	●
1"3/4	100×1	●	●
2"	100×1	●	●
2"1/2	100×1	●	●
3"	100×1	●	●

#5			
長さ	入り数	鉄	ステンレス
1/8	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
5/8	100×1	●	●
3/4	100×1	●	●
7/8	100×1	●	●
1"	100×1	●	●
1"1/4	100×1	●	●
1"1/2	100×1	●	●
2"	100×1	●	●
2"1/2	100×1	●	●

#6			
長さ	入り数	鉄	ステンレス
14	1000×14	●	●
16	1000×10	●	●
1/8	100×1	●	●
3/16	100×1	●	●
1/4	100×1	●	●
5/16	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
3/8	100×1	●	●
7/16	100×1	●	●
1/2	100×1	●	●
5/8	100×1	●	●
3/4	100×1	●	●
7/8	100×1	●	●
1"	100×1	●	●
1"1/8	100×1	●	●
1"1/4	100×1	●	●
1"3/8	100×1	●	●
1"1/2	100×1	●	●
1"3/4	100×1	●	●
2"	100×1	●	●
2"1/4	100×1	●	●
2"1/2	100×1	●	●
3"	100×1	●	●