

AS568 (ARP568) 航空機用 Oリング (パッキンおよびガスケット)

AS568 呼び番号	Oリング呼び寸法(in)			Oリング実寸法(mm)						AN 6227 1516	AN 6230 1517	AS 568 呼び番号
	W	d	D	d ₂	d ₁	材質群別許容差						
						①	②	③				
001	1/32	1/32	3/32	1.02	±0.07	0.74	±0.10	±0.20	±0.30			001
002	3/64	3/64	9/64	1.27		1.07	±0.10	±0.20	±0.30			002
003	1/16	1/16	3/16	1.52		1.42	±0.10	±0.20	±0.30			003
004	1/16	5/64	13/64	1.78		1.78	±0.12	±0.24	±0.36			004
005	1/16	3/32	7/32			2.57	±0.12	±0.24	±0.36			005
006	1/16	1/8	1/4			2.90	±0.12	±0.24	±0.36	1		006
007	1/16	5/32	9/32			3.68	±0.12	±0.24	±0.36	2		007
008	1/16	3/16	5/16			4.47	±0.12	±0.24	±0.36	3		008
009	1/16	7/32	11/32			5.28	±0.12	±0.24	±0.36	4		009
010	1/16	1/4	3/8			6.07	±0.12	±0.24	±0.36	5		010
011	1/16	5/16	7/16			7.65	±0.12	±0.24	±0.36	6		011
012	1/16	3/8	1/2			9.25	±0.12	±0.24	±0.36	7		012
013	1/16	7/16	9/16			10.82	±0.12	±0.24	±0.36			013
014	1/16	1/2	5/8			12.42	±0.12	±0.24	±0.36			014
015	1/16	9/16	11/16			14.00	±0.12	±0.24	±0.36			015
016	1/16	5/8	3/4			15.60	±0.12	±0.24	±0.36			016
017	1/16	11/16	13/16			17.17	±0.12	±0.24	±0.36			017
018	1/16	3/4	7/8			18.77	±0.12	±0.24	±0.36			018
019	1/16	13/16	15/16			20.35	±0.15	±0.30	±0.45			019
020	1/16	7/8	1			21.95	±0.15	±0.30	±0.45			020
021	1/16	15/16	1 1/16			23.52	±0.15	±0.30	±0.45			021
022	1/16	1	1 1/8			25.12	±0.15	±0.30	±0.45			022
023	1/16	1 1/16	1 3/16			26.70	±0.15	±0.30	±0.45			023
024	1/16	1 1/8	1 1/4			28.30	±0.15	±0.30	±0.45			024
025	1/16	1 3/16	1 5/16			29.87	±0.15	±0.30	±0.45			025
026	1/16	1 1/4	1 3/8			31.47	±0.15	±0.30	±0.45			026
027	1/16	1 5/16	1 7/16			33.05	±0.15	±0.30	±0.45			027
028	1/16	1 3/8	1 1/2			34.65	±0.15	±0.30	±0.45			028
029	1/16	1 1/2	1 5/8			37.82	±0.25	±0.50	±0.75			029
030	1/16	1 5/8	1 3/4			41.00	±0.25	±0.50	±0.75			030
031	1/16	1 3/4	1 7/8			44.17	±0.25	±0.50	±0.75			031
032	1/16	1 7/8	2			47.35	±0.25	±0.50	±0.75			032
033	1/16	2	2 1/8			50.52	±0.25	±0.50	±0.75			033
034	1/16	2 1/8	2 1/4			53.70	±0.25	±0.50	±0.75			034
035	1/16	2 1/4	2 3/8			56.87	±0.25	±0.50	±0.75			035
036	1/16	2 3/8	2 1/2			60.05	±0.25	±0.50	±0.75			036
037	1/16	2 1/2	2 5/8			63.22	±0.25	±0.50	±0.75			037
038	1/16	2 5/8	2 3/4			66.40	±0.25	±0.50	±0.75			038
039	1/16	2 3/4	2 7/8			69.57	±0.38	±0.76	±1.14			039
040	1/16	2 7/8	3			72.75	±0.38	±0.76	±1.14			040
041	1/16	3	3 1/8			75.92	±0.38	±0.76	±1.14			041
042	1/16	3 1/4	3 3/8			82.27	±0.38	±0.76	±1.14			042
043	1/16	3 1/2	3 5/8			88.62	±0.38	±0.76	±1.14			043

AS