


鋼 六角穴付き止めねじ(ホーローセット) (平先)[TKS] 東工舎金属製作所製



A000501T

鉄



注(1) lが下の表に示す階段状の点線より短いものは、120°の面取りとする。
 (2) 45°の角度は、おねじの谷の径より下の傾斜部に適用する。

(mm)

ねじの呼び(d)	M1.6	M2	M2.5(2.6)	M3	M4	M5	M6	M8	M10	M12	M14	M16	M18	M20	M24		
ピッチ(P)	0.35	0.4	0.45	0.5	0.7	0.8	1.0	1.25	1.50	1.75	2.0	2.0	2.5	2.5	3.0		
dp	最大(基準寸法)	0.8	1.0	1.5	2.0	2.5	3.5	4.0	5.5	7.0	8.5	12.0	12.0	13.0	15.0	18.0	
	最小	0.55	0.75	1.25	1.75	2.25	3.2	3.7	5.2	6.64	8.14	9.64	11.57	12.57	14.57	17.57	
df	約 おねじの谷径																
e	最小	0.803	1.003	1.427	1.73	2.30	2.87	3.44	4.58	5.72	6.86	6.86	9.15	—	11.43	13.72	
s	呼び(基準寸法)	0.7	0.9	1.3	1.5	2.0	2.5	3.0	4.0	5.0	6.0	6.0	8.0	8.0	10.0	12.0	
	最小	0.711	0.889	1.270	1.520	2.020	2.520	3.020	4.020	5.020	6.020	6.020	8.025	8.025	10.025	12.032	
	最大	0.724	0.902	1.295	1.545	2.045	2.560	3.080	4.095	5.095	6.095	6.095	8.115	8.115	10.115	12.142	
t	最小 ⁽³⁾	1欄	0.7	0.8	1.2	1.2	1.5	2.0	2.0	3.0	4.0	4.8	4.8	6.4	7.2	8.0	10.0
		2欄	1.5	1.7	2.0	2.0	2.5	3.0	3.5	5.0	6.0	8.0	8.0	10.0	11.0	12.0	15.0

長さ	入り数	生地
2	1000×30	●
3	1000×30	●
4	1000×30	●
5	1000×30	●
6	1000×30	●
8	1000×30	●
10	1000×30	●

長さ	入り数	生地	三番ホーロー
2.5	1000×30	●	●
3	1000×30	●	●
4	1000×30	●	●
5	1000×30	●	●
6	1000×30	●	●
8	1000×30	●	●

長さ	入り数	生地
3	1000×30	●
4	1000×30	●
5	1000×30	●
6	1000×30	●
8	1000×30	●
10	1000×30	●
12	1000×26	●
14	1000×26	●
15	1000×26	●
16	1000×26	●
18	1000×26	●
20	1000×26	●
22	1000×20	●
25	1000×20	●
30	1000×18	●

長さ	入り数	生地	三番ホーロー
3	1000×30	●	●
4	1000×30	●	●
5	1000×30	●	●
6	1000×30	●	●
8	1000×26	●	●
10	1000×26	●	●
12	1000×26	●	●
14	1000×20	●	●
15	1000×20	●	●
16	1000×20	●	●
18	1000×18	●	●
20	1000×18	●	●
22	1000×9	●	●
25	1000×9	●	●
30	1000×9	●	●
50	500×10	●	●

長さ	入り数	生地
4	1000×26	●
5	1000×26	●
6	1000×26	●
8	1000×26	●
10	1000×20	●
12	1000×20	●
14	500×18	●
15	500×18	●
16	500×18	●
20	500×18	●
22	500×18	●
25	500×10	●
30	500×10	●

長さ	入り数	生地
5	500×26	●
6	500×26	●
8	500×26	●
10	500×26	●
12	500×20	●
14	500×20	●
15	500×18	●
16	500×18	●
18	500×18	●
20	500×10	●
22	500×10	●
25	500×10	●
30	200×18	●
35	200×18	●
40	200×18	●
45	200×10	●
50	200×10	●
55	200×10	●
60	200×10	●
65	200×10	●
70	100×18	●
75	100×18	●
80	100×10	●
85	120×10	●
90	120×10	●
100	100×10	●

長さ	入り数	生地
6	500×26	●
8	500×20	●
10	500×18	●
12	500×18	●
14	200×18	●
15	200×18	●
16	200×18	●
18	200×18	●
20	200×18	●
22	200×18	●
25	200×18	●
30	200×10	●
35	200×10	●
40	200×10	●
45	100×18	●
50	100×18	●
55	100×18	●
60	100×9	●
65	100×9	●
70	100×9	●
75	100×9	●
80	80×9	●
85	60×9	●
90	60×9	●

長さ	入り数	生地
8	500×18	●
10	500×10	●
12	500×10	●
14	200×18	●
15	200×18	●
16	200×18	●
18	200×10	●
20	200×10	●
25	200×10	●
30	100×18	●
35	100×18	●
40	100×18	●
45	100×9	●
50	100×9	●
55	50×18	●
60	50×18	●
65	50×18	●
70	40×18	●
75	40×18	●
80	40×18	●
85	30×18	●

長さ	入り数	生地
10	500×10	●
12	200×18	●
14	200×18	●
15	200×10	●
16	200×10	●
18	200×10	●
20	200×10	●
22	200×10	●
25	200×10	●
30	100×10	●
35	100×10	●
40	100×10	●
45	100×6	●
50	100×6	●
55	100×6	●
60	50×9	●
65	50×9	●
70	50×9	●
75	50×9	●
80	50×9	●

長さ	入り数	生地
14	200×9	●
15	200×6	●
16	200×6	●
18	200×6	●
20	200×6	●
22	100×10	●
25	100×10	●
30	100×10	●
35	100×6	●
40	100×6	●
45	50×9	●
50	40×9	●
55	40×9	●
60	50×6	●
65	50×6	●
70	50×6	●
75	50×6	●

長さ	入り数	生地	三番ホーロー
15	200×6	●	●
16	200×6	●	●
18	100×9	●	●
20	100×9	●	●
22	100×6	●	●
25	100×6	●	●
30	100×6	●	●
35	50×9	●	●
40	50×9	●	●
45	50×6	●	●
50	50×6	●	●
55	50×6	●	●
60	50×6	●	●
65	40×6	●	●
70	40×6	●	●
75	40×6	●	●
80	40×6	●	●

長さ	入り数	生地
20	50×9	●
25	50×9	●
30	50×6	●
35	50×6	●
40	50×6	●
45	40×6	●
50	40×6	●
55	30×6	●
60	30×6	●
65	25×6	●
70	25×6	●
75	20×6	●
80	20×6	●
85	20×6	●
100	20×6	●