


B-1 JIS Vプーリー - B・BX適用

WEB 選定ナビ WEB CAD Download



単位: mm

品番	価格 (円)	呼び径 dm	外径 de	最大軸穴径 d	下穴径 d	形状 図番	ハブ				リム		慣性モーメント (kg・m ²)	質量 (kg)
							db	l	s1	s2	w	h ⁺² ₀		
63-B-1	1,060	63	74	25	-	11U	45	40	15	-	25	-	0.000358	0.74
71-B-1	1,180	71	82	25	-	21U	45	32	15	8	25	20	0.000517	0.81
75-B-1	1,260	75	86	25	-	21U	45	32	15	8	25	20	0.000622	0.88
80-B-1	1,420	80	91	28	-	21U	50	32	15	8	25	20	0.000802	1.01
90-B-1	1,650	90	101	28	-	21U	50	32	15	8	25	20	0.0012	1.2
100-B-1	2,050	100	111	32	-	21U	56	32	15	8	25	20	0.00179	1.46
106-B-1	2,230	106	117	32	-	21U	56	32	15	8	25	20	0.00221	1.6
112-B-1	2,240	112	123	32	-	21U	56	32	15	8	25	20	0.00269	1.74
118-B-1	2,350	118	129	32	-	21U	56	32	15	8	25	20	0.00326	1.89
125-B-1	2,390	125	136	32	-	23U	56	32	15	8	25	20	0.00336	1.65
132-B-1	2,500	132	143	32	-	23U	56	32	15	8	25	20	0.00402	1.74
135-B-1	2,720	135	146	32	-	20U	56	32	15	8	25	20	0.00433	1.78
140-B-1	2,670	140	151	32	-	20U	56	32	15	8	25	20	0.00488	1.85
145-B-1	2,880	145	156	32	-	20U	56	32	15	8	25	20	0.00549	1.93
150-B-1	2,940	150	161	32	-	20U	56	32	15	8	25	20	0.00614	2
155-B-1	3,280	155	166	32	-	20U	56	32	15	8	25	20	0.00686	2.08
160-B-1	3,320	160	171	35.5	-	10U	63	35	10	-	25	20	0.00778	2.36
165-B-1	3,510	165	176	35.5	-	10U	63	35	10	-	25	20	0.00864	2.44
170-B-1	3,550	170	181	35.5	-	10U	63	35	10	-	25	20	0.00954	2.52
180-B-1	4,100	180	191	35.5	-	10U	63	35	10	-	25	20	0.0119	2.79
190-B-1	4,390	190	201	35.5	-	10U	63	35	10	-	25	20	0.0143	2.98

追加工サービスをご利用ください。

Vプーリーに軸穴・キー溝・押しねじ穴の追加工をいたします。実働1日目出荷。

→ P.304



● 軸穴・キー溝・押しねじ追加工 → P.304

対応可・別料金

● 品番指定



直送



14時当日出荷



NBK ネットショップ

100-B-1

1