



精密平行ブロック

PRECISION PARALLELS No.E-9158

RoHS対応



▽▽▽ (▽▽▽)



材質 S50C・FC300

熱処理 HP1~8:焼入HRC50±3 HP21~34:焼入HRC50±3
HP9~20:焼鈍

- 両端面を除く4面を研削仕上げ。
- 平行ブロックの利用により加工ワークが安定し、平行度が確保されますので精密加工が可能になり、能率がアップします。

参照ページ



仕様・価格表

* 標準在庫品 1個価格

オーダーNo.	No.	A ^{+0.03} ₀	B ^{+0.01} ₀	C	D	E	材質	質量kg	価格
* 901242	HP 1	10	20	150	0.012	0.006	S50C	0.2	9,150
* 901243	HP 2	15	20	150	0.012	0.006	S50C	0.4	11,600
* 901244	HP 3	15	30	150	0.012	0.006	S50C	0.5	12,200
* 901245	HP 4	20	30	150	0.012	0.006	S50C	0.7	12,200
* 901246	HP 5	25	50	150	0.012	0.006	S50C	1.5	12,200
* 901247	HP 6	15	30	250	0.013	0.007	S50C	0.9	14,900
* 901248	HP 7	20	30	250	0.013	0.007	S50C	1.2	14,900
* 901249	HP 8	25	50	250	0.013	0.007	S50C	2.4	17,700
* 901250	HP 9	25	50	300	0.014	0.008	FC300	2.7	18,600
* 901251	HP10	40	50	300	0.014	0.008	FC300	4.4	19,700
* 901252	HP11	40	75	300	0.014	0.008	FC300	6.6	19,700
* 901253	HP12	50	50	100	0.012	0.006	FC300	1.8	12,200
* 901254	HP13	50	50	150	0.012	0.006	FC300	2.7	13,200
* 901255	HP14	50	50	250	0.013	0.007	FC300	4.6	16,500
* 901256	HP15	50	100	150	0.012	0.006	FC300	5.5	16,500
* 901257	HP16	50	100	250	0.013	0.007	FC300	9.1	25,300
* 901258	HP17	50	100	300	0.014	0.008	FC300	11.0	29,700
* 901259	HP18	100	100	150	0.012	0.006	FC300	11.0	29,700
* 901260	HP19	100	100	250	0.013	0.007	FC300	18.3	42,800
* 901261	HP20	100	100	300	0.014	0.008	FC300	21.9	52,000
* 900098	HP21	12	25	150	0.012	0.006	S50C	0.4	11,900
* 900100	HP22	10	20	200	0.013	0.007	S50C	0.3	11,100
* 900101	HP23	15	20	200	0.013	0.007	S50C	0.5	13,100
* 900102	HP24	15	30	200	0.013	0.007	S50C	0.7	14,000
* 900103	HP25	20	30	200	0.013	0.007	S50C	0.9	14,000
* 900104	HP26	25	50	200	0.013	0.007	S50C	2.0	16,700
* 934589	HP27	8	15	100	0.010	0.005	S50C	0.1	7,750
* 934590	HP28	10	20	100	0.010	0.005	S50C	0.2	8,850
* 934591	HP29	10	25	100	0.010	0.005	S50C	0.2	9,000
* 934592	HP30	15	35	100	0.010	0.005	S50C	0.4	10,300
* 934593	HP31	8	15	125	0.012	0.006	S50C	0.1	9,100
* 934594	HP32	10	20	125	0.012	0.006	S50C	0.2	10,500
* 934595	HP33	10	30	125	0.012	0.006	S50C	0.3	10,800
* 934596	HP34	15	40	125	0.012	0.006	S50C	0.6	12,300