


鉄 皿ばね座金(キャップ用 軽荷重用)



小ねじ
メソコねじ
組込みねじ
タツピンねじ
タツタイト
ハエタねじ
いたすら防止ねじ
建材用スクリュー
ボルト
キャップボルト
ドリルねじ
座金
つまみねじ
ナット
樹脂製品
アンカーボルト

W2000020

鉄



呼び	入り数	生地	三価ホワイト	ニッケル	クロム
CDW-M3-L	30000×5	●	●	●	●
CDW-M4-L	20000×5	●	●	●	●
CDW-M5-L	10000×5	●	●	●	●
CDW-M6-L	10000×5	●	●	●	●
CDW-M8-L	5000×5	●	●	●	●
CDW-M10-L	2000×5	●	●	●	●
CDW-M12-L	2000×5	●	●	●	●
CDW-M14-L	1200×5	●	●	●	●
CDW-M16-L	800×5	●	●	●	●
CDW-M18-L	500×5	●	●	●	●
CDW-M20-L	400×5	●	●	●	●
CDW-M22-L	250×5	●	●	●	●
CDW-M24-L	200×5	●	●	●	●
CDW-M27-L	200×5	●	●	●	●
CDW-M30-L	100×5	●	●	●	●
CDW-M33-L	80×5	●	●	●	●
CDW-M36-L	70×5	●	●	●	●
CDW-M39-L	50×5	●	●	●	●


呼び	d		D		t		H	試験荷重 kN
	基本寸法	許容差	基本寸法	許容差	基本寸法	許容差	基本寸法	
CDW-M3-L	3.20	+0.25 0	5.5	0 -0.25	0.45	±0.035	0.60	1.03
CDW-M4-L	4.25		7.0		0.50	±0.035	0.70	1.77
CDW-M5-L	5.25		8.5		0.60	±0.04	0.85	2.94
CDW-M6-L	6.40	+0.3 0	10.0	0 -0.3	0.70	±0.045	1.00	4.12
CDW-M8-L	8.40		13.0		0.80	±0.05	1.20	7.45
CDW-M10-L	10.60		16.0		1.00	±0.055	1.50	11.77
CDW-M12-L	12.60	+0.4 0	18.0	0 -0.4	1.20	±0.065	1.70	17.65
CDW-M14-L	14.60		21.0		1.40	±0.07	1.95	23.54
CDW-M16-L	16.90		24.0		1.60	±0.08	2.25	32.36
CDW-M18-L	18.90		27.0		1.807	±0.085	2.55	39.23
CDW-M20-L	20.90		30.0		2.00	±0.09	2.80	49.03
CDW-M22-L	22.90	+0.5 0	33.0	0 -0.5	2.30	±0.10	3.10	61.78
CDW-M24-L	25.40		36.0		2.50		3.40	71.59
CDW-M27-L	28.20		40.0		2.60	±0.11	3.70	93.16
CDW-M30-L	31.20		45.0		3.00		4.20	117.68
CDW-M33-L	34.50	+0.50 0	50.0	0 -0.5	3.20	±0.11	4.60	137.29
CDW-M36-L	37.50		54.0		3.50		5.00	166.71
CDW-M39-L	40.50		58.0		3.80		5.40	196.13

鉄 皿ばね座金(キャップ用 重荷重用)



W2000021

鉄



呼び	入り数	生地	三価ホワイト	ニッケル	クロム
CDW-M6-H	6000×5	●	●	●	●
CDW-M8-H	3000×5	●	●	●	●
CDW-M10-H	2000×5	●	●	●	●
CDW-M12-H	1000×5	●	●	●	●
CDW-M14-H	700×5	●	●	●	●
CDW-M16-H	500×5	●	●	●	●
CDW-M18-H	300×5	●	●	●	●
CDW-M20-H	250×5	●	●	●	●
CDW-M22-H	200×5	●	●	●	●
CDW-M24-H	150×5	●	●	●	●
CDW-M27-H	100×5	●	●	●	●
CDW-M30-H	100×5	●	●	●	●

呼び	d		D		t		H	試験荷重 kN
	基本寸法	許容差	基本寸法	許容差	基本寸法	許容差	基本寸法	
CDW-M6-H	6.4	+0.3 0	10	0 -0.3	1	±0.055	1.25	8.24
CDW-M8-H	8.4		13		1.2	±0.065	1.55	14.71
CDW-M10-H	10.6		16		1.5	±0.075	1.9	23.54
CDW-M12-H	12.6		18		1.8	±0.085	2.2	34.32
CDW-M14-H	14.6	+0.4 0	21	0 -0.4	2	±0.09	2.5	47.07
CDW-M16-H	16.9		24		2.3	±0.10	2.8	63.74
CDW-M18-H	18.9		27		2.6		3.15	78.45
CDW-M20-H	20.9		30		2.8	±0.11	3.55	98.07
CDW-M22-H	22.9	+0.5 0	33	0 -0.5	3.2		3.9	122.58
CDW-M24-H	25.4		36		3.5		4.25	142.2
CDW-M27-H	28.2		40		3.8		4.75	186.33
CDW-M30-H	31.2		45		4.2		5.2	225.55