


●鋼からステンレス鋼、アルミまで、高速・高効率加工ができます。

This drill having stub length is useful in material from Carbon Steel and Stainless Steel to Aluminum.



LIST 6548

オーダー方法 **商品記号**

単位 (Unit) : mm

商品記号 Code	直径 Dc	溝長 ℓ	首下 L1	全長 L	シャンク径 Ds	在庫 Stock	参考価格(円) Price (¥)
AGESS1.0	1.0	6	6.5			●	1,150
AGESS1.01	1.01					-	
AGESS1.02	1.02					-	
AGESS1.03	1.03					-	
AGESS1.04	1.04					-	
AGESS1.05	1.05					□	-
AGESS1.06	1.06					-	
AGESS1.07	1.07					-	
AGESS1.08	1.08					-	
AGESS1.09	1.09	-					
AGESS1.1	1.1	7	7.5			●	1,050
AGESS1.11	1.11					-	
AGESS1.12	1.12					-	
AGESS1.13	1.13					-	
AGESS1.14	1.14					-	
AGESS1.15	1.15					□	-
AGESS1.16	1.16					-	
AGESS1.17	1.17					-	
AGESS1.18	1.18					-	
AGESS1.19	1.19	-					
AGESS1.2	1.2	8	8.5	40		●	1,050
AGESS1.21	1.21					-	
AGESS1.22	1.22					-	
AGESS1.23	1.23					-	
AGESS1.24	1.24					-	
AGESS1.25	1.25					□	-
AGESS1.26	1.26					-	
AGESS1.27	1.27					-	
AGESS1.28	1.28					-	
AGESS1.29	1.29	-					
AGESS1.3	1.3				3	●	1,050
AGESS1.31	1.31					-	
AGESS1.32	1.32					-	
AGESS1.33	1.33					-	
AGESS1.34	1.34					-	
AGESS1.35	1.35					□	-
AGESS1.36	1.36					-	
AGESS1.37	1.37					-	
AGESS1.38	1.38					-	
AGESS1.39	1.39	-					
AGESS1.4	1.4	9	9.5			●	1,050
AGESS1.41	1.41					-	
AGESS1.42	1.42					-	
AGESS1.43	1.43					-	
AGESS1.44	1.44					-	
AGESS1.45	1.45					□	-
AGESS1.46	1.46					-	
AGESS1.47	1.47					-	
AGESS1.48	1.48					-	
AGESS1.49	1.49	-					
AGESS1.5	1.5	10	11	44		●	1,050
AGESS1.51	1.51					-	
AGESS1.52	1.52					-	
AGESS1.53	1.53					-	
AGESS1.54	1.54					-	
AGESS1.55	1.55					□	-
AGESS1.56	1.56					-	
AGESS1.57	1.57					-	
AGESS1.58	1.58					-	
AGESS1.59	1.59	-					
AGESS1.6	1.6	10	11			●	943
AGESS1.61	1.61					-	
AGESS1.62	1.62					-	
AGESS1.63	1.63					-	
AGESS1.64	1.64					-	
AGESS1.65	1.65					□	-
AGESS1.66	1.66					-	
AGESS1.67	1.67					-	
AGESS1.68	1.68					-	
AGESS1.69	1.69	-					
AGESS1.7	1.7	11	12			●	943
AGESS1.71	1.71					-	
AGESS1.72	1.72					-	
AGESS1.73	1.73					-	
AGESS1.74	1.74					-	
AGESS1.75	1.75					□	-
AGESS1.76	1.76					-	
AGESS1.77	1.77					-	
AGESS1.78	1.78					-	
AGESS1.79	1.79	-					
AGESS1.8	1.8	11	12	44	3	●	943
AGESS1.81	1.81					-	
AGESS1.82	1.82					-	
AGESS1.83	1.83					-	
AGESS1.84	1.84					-	
AGESS1.85	1.85					□	-
AGESS1.86	1.86					-	
AGESS1.87	1.87					-	
AGESS1.88	1.88					-	
AGESS1.89	1.89	-					
AGESS1.9	1.9				3	●	943
AGESS1.91	1.91					-	
AGESS1.92	1.92					-	
AGESS1.93	1.93					-	
AGESS1.94	1.94					-	
AGESS1.95	1.95					□	-
AGESS1.96	1.96					-	
AGESS1.97	1.97					-	
AGESS1.98	1.98					-	
AGESS1.99	1.99	-					
AGESS2.0	2.0	12	13.5			●	943
AGESS2.01	2.01					-	
AGESS2.02	2.02					-	
AGESS2.03	2.03					-	
AGESS2.04	2.04					-	
AGESS2.05	2.05					□	-
AGESS2.06	2.06					-	
AGESS2.07	2.07					-	
AGESS2.08	2.08					-	
AGESS2.09	2.09	-					
AGESS2.1	2.1	13	14.5			●	1,120
AGESS2.11	2.11					-	
AGESS2.12	2.12					-	
AGESS2.13	2.13					-	
AGESS2.14	2.14					-	
AGESS2.15	2.15					□	-
AGESS2.16	2.16					-	
AGESS2.17	2.17					-	
AGESS2.18	2.18					-	
AGESS2.19	2.19	-					